



Connectors > Rectangular Connectors > Connector Contacts



Contact Type: **Pin**
Contact Mating Area Plating Material: **Silver**
Wire Contact Termination Area Plating Material: **Silver**
Wire Size: **35 – 55 mm²**

Features

Contact Features

Contact Type	Pin
Contact Mating Area Plating Material	Silver
Wire Contact Termination Area Plating Material	Silver
Contact Current Rating (Max)	150 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Dimensions

Wire Size	35 – 55 mm²
-----------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (1.2% in Contact Lead-Copper Alloy) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.



Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #205163-1
RECEPT ASSY,15 POSN,AMPLIMITE




TE Part #0662-207-0482
CONT SOC ASSY



TE Part #0662-207-0082
CONT SOC ASSY



TE Part #0662-207-0882
CONT SOC ASSY



TE Part #218560-001
22759/34-01-9



TE Part #322333
TERMINAL,SOLIS R HT 16-14 6



TE Part #1925220-9
TMN2N051PC2DM018S = M32139/03-G05SNS



TE Part #YDTS26W25-35PBV001
D38999: Straight Plug, 25-35 Insert



TE Part #1662-213-1631
CONT SOC ASSY



TE Part #391961-000
55PC0811-22-9CS2637

Documents

Product Drawings
CONT PIN



English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_0660-206-0082_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_0660-206-0082_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_0660-206-0082_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

DEUTSCH High Power Contacts for MIL-DTL-5015

English