



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



SolderSleeve Shield Terminator Product Type: **Shield Terminator**

SolderSleeve Shield Terminator Operating Temperature (Max): **125 °C**

SolderSleeve Shield Terminator Expanded Inside Diameter (Min): **7.11 mm [.28 in]**

SolderSleeve Shield Terminator Recovered Inside Diameter (Max): **3.56 mm [.14 in]**

Pre-Installed Lead: **No**

Features

Product Type Features

Splice Type	SolderSleeve
Temperature Indicator	No
Temperature Indicator Type	None
SolderSleeve Shield Terminator Product Type	Shield Terminator

Configuration Features

Pre-Installed Lead	No
--------------------	----

Dimensions

SolderSleeve Shield Terminator Expanded Inside Diameter (Min)	7.11 mm[.28 in]
SolderSleeve Shield Terminator Recovered Inside Diameter (Max)	3.56 mm[.14 in]

Usage Conditions

SolderSleeve Shield Terminator Operating Temperature (Max)	125 °C
Resistance Properties	Moisture/Spray Protection
Wire Temperature (Max)	125 °C

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (32% in Solder) Cd (18% in Solder) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>





Compatible Parts



TE Part # CJ2087-000
[HL2010E-KIT-120V](#)

Customers Also Bought



 TE Part #205558-2 AMPLIMITE, ASY, PLUG, STD, 109, 2	 TE Part #1643906-1 Crown Clip Senior 538-17-00100 399-01 7	 TE Part #1-480585-0 09P .140 MNL PLUG NAT	 TE Part #1-967412-2 TIMER, CONNECTOR HOUSING
 TE Part #1-968849-2 AMP MCP, RECEPTACLE AND TAB	 TE Part #109858-000 D-181-1222-90/9	 TE Part #054955-000 CWT-9001	 TE Part #114163-000 CWT-9003
 TE Part #YDTS33Z17RV0010000 CAP ASSEMBLY	 TE Part #1571095-1 PRCSA1-20F-BB000, POWER ROCKER		

Documents

Product Drawings
CWT-9005

English

Datasheets & Catalog Pages
1654025_Sec8_B-155_CWT_D-110_D-1744

English

Raychem Electrical Interconnect Products
English

Product Specifications
SolderSleeve One-Step Wire and Cable Terminators Installation Procedures for CWT and B-155 Products
English