



Connectors > RF Coax Connectors > RF Connectors



RF Interface: **SMA**

RF Connector Style: **Plug**

RF Connector Mated Outer Diameter (Approximate): **6.35 mm [.25 in]**

Impedance: **50 Ω**

Compatible With RF Cable Type: **RG 402 Semi-Rigid**

Features

Product Type Features

Connector Product Type	Housing
RF Interface	SMA
RF Connector Style	Plug
Compatible With RF Cable Type	RG 402 Semi-Rigid
Connector System	Cable-to-Cable
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Connector Seal Type	Gasket

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Cable Connector Orientation	Straight
Body Material	Stainless Steel
Body Plating Material	Gold

Termination Features

--	--



Termination Method to Wire & Cable	Solder
------------------------------------	--------

Mechanical Attachment

RF Connector Coupling Mechanism	Threaded
Connector Mounting Type	Cable Mount (Free-Hanging)
RF Contact Captivation Method	Mechanical
Detent	Without

Dimensions

Product Length	11.2 mm[.442 in]
RF Connector Mated Outer Diameter (Approximate)	6.35 mm[.25 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Operating Frequency	18 GHz
---------------------	--------

Packaging Features

Packaging Method	Package
------------------	---------

Other

Coupling Nut Plating Material	Gold over Nickel
Gasket Material	Silicone Rubber
Coupling Nut Base Material	Stainless Steel
Dielectric Material	TFE Fluorocarbon

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1051644-1 2031 5003 02	 TE Part # 1055070-1 2088 1230 02	 TE Part # 1054874-1 2084 1100 00	 TE Part # 221789-1 JACK,PCB,SERIES SMA
 TE Part # 1052566-1 2052 1618 02,SMA FM JACK RECPT	 TE Part # 1053221-1 2058 5029 00	 TE Part # 1054426-1 2082 5133 02	 TE Part # 221790-1 JACK,RIGHT ANGLE,PCB,SMA
 TE Part # 1054868-1 2084 0000 00	 TE Part # 1053072-1 2056 0000 00	 TE Part # 1050547-1 2001 5032 00	 TE Part # 1050548-1 2001 5032 02



TE Part # 6274096-1
JACK ASSEMBLY, ACTION PIN, SMA

TE Part # 1053378-1
2064 0000 00

TE Part # 1050525-1
2001 5003 02,SMA CABLE PLUG

TE Part # 1052639-1
2052 3357 02

TE Part # 2081005-1
ASSY. SMA JACK PCB EDGE MOUNT

TE Part # 1050611-1
2001 5443 02

TE Part # 1050740-1
2001 7641 02

TE Part # 1052422-1
2052 0000 02,SMA FM JACK RECPT

Also in the Series | AMP SMA

Battery Holders(1)

Between Series Adapters(3)

Coax Contacts(1)

Coax Terminators(1)

In-Series Adapters(35)

Rack & Panel Ferrules & Inserts(1)

RF Cable Assemblies(2)

RF Connector Hardware(2)

RF Connector Launchers(13)

RF Connector Shrouds(10)

RF Connectors(527)

Customers Also Bought





TE Part #808222-000
Heat Shrink Boots: Non Lipped, Straight




TE Part #4515DO-DS3BK004GP
BOARD LEVEL PRESSURE STOCK LIST




TE Part #608315-000
Heat Shrink Boots: Lipped, Straight




TE Part #YDTS24G17-08PNV001
D38999: Jam Nut, 17-08 Insert



TE Part #1532269-1
M83513/22-D01CN = MCKS-C2-B-25PST1



TE Part #1532272-5
M83513/23-G02CN = MCKS-C2-B-51PST1A



TE Part #1532277-1
M83513/25-D01CN = MCKS-C2-B-25SST1



TE Part #2-327137-2
T-SHIELD FERR.,.130-.145



TE Part #658466-000
SO63-2-55-24-0



TE Part #C51203-000
TXR40AC90-1010BI

Documents

Product Drawings

2001 5025 00

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1050536-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1050536-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1050536-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance



TE Material Declaration

English

Instruction Sheets

Instruction Sheet (U.S.)

English

OSM Straight Cable Plug Retractable Coupling Nut Direct Solder Attachment 1050537-1, 1050559-1, 1050560-1, 1045437-1, 1050422-1, 1050536-1, and 1050537-1

English