




Connectors > D-Shaped Connectors > D-Sub Connectors > PCB D-Sub Connectors > D-Sub Plug Assembly: Standard, Vertical, 1.27mm



Connector & Housing Type: **Plug**

Connector System: **Board-to-Board**

Number of Positions: **60**

Centerline (Pitch): **1.27 mm [.05 in]**

Number of Rows: **2**

[All D-Sub Plug Assembly: Standard, Vertical, 1.27mm \(28\)](#)

Features

Product Type Features

Flux Drain Holes	With
Shell Type	All Plastic
Connector & Housing Type	Plug
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board
Shielded	No
Connector Type	Connector Assembly
Product Type	Connector

Configuration Features

Number of Positions	60
Number of Rows	2
PCB Mount Orientation	Vertical

Body Features

Post Plating Material	Tin over Nickel
Connector Profile	Standard

Contact Features

Contact Mating Area Plating Material	Gold
--------------------------------------	------



Contact Base Material	Copper Alloy
Contact Shape & Form	Rectangular
	30 µin

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Post Length	3.1 mm[.122 in]

Mechanical Attachment

PCB Mount Alignment	Without
PCB Mount Retention	Without
Mating Retention	Without
Connector Mounting Type	Board Mount
Mating Alignment	Without

Housing Features

Centerline (Pitch)	1.27 mm[.05 in]
Housing Material	PBT
Housing Color	Black

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tray
Packaging Quantity	80

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-020-ADRV127
AMPLIMITE D-Sub Receptacle
Assembly: Vertical, 1.27mm

TE Part # CAT-018-DRARA127
D-Sub Receptacle Assembly: Right
Angle, 1.27mm

Also in the Series | AMPLIMITE 0.50 Series

D-Sub Backshells & Clamps(31)

D-Sub Covers(20)

D-Sub Locking & Mounting(8)

IDC D-Sub Connectors(77)



Insertion & Extraction Tools(1)

PCB D-Sub Connectors(196)

Customers Also Bought

TE Part #6-5174215-4
AMPLIMITE D-Sub Receptacle
Assembly: Vertical, 1.27mm

TE Part #5177984-9
Free Height Plug Connector: Board-Board, Vertical, 180, 0.8mm

TE Part #YDTS26Z15-05PAV001
D38999: Straight Plug, 15-05 Insert

TE Part #1624316-2
SP3 1R0 5% TAPED

TE Part #1-87962-9
40 MODII HORZ DR CE 100CL/115

TE Part #2-1415546-8
RM622024

TE Part #5767057-7
MICT,495,PLUG,266,PDNI

TE Part #6-1617804-1
FCAV-325-BZ3=3PDT 25A MID-RANGE RELAY

TE Part #2-1624292-2
SP1 13R 1% TAPED

TE Part #3830903001
44A1131-24-0/2/6-9

Documents

Product Drawings
AMPLIMITE.050 CAP ASS'Y (V) 60P PB-FREE
English

CAD Files
3D PDF
English
Customer View Model
ENG_CVM_6-5174216-4_O.2d_dxf.zip



English

Customer View Model

[ENG_CVM_6-5174216-4_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_6-5174216-4_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

TS100 2X3 POS MARK II CABLE CONNECTOR

English

Product Specification

English

Product Specification

English