

## AMPLIMITE | AMPLIMITE HDP

TE Internal #: 5747022-2

AMPLIMITE HDP, PCB D-Sub Connectors, Plug, Board-to-Board, 25

Position, 2.74mm [.108in] Centerline, 2 Row, Row-to-Row Spacing

2.84 mm [.112 in]

View on TE.com >



Connectors > D-Shaped Connectors > D-Sub Connectors > PCB D-Sub Connectors >

D-Sub Plug Assembly: Standard, Right Angle, Shell Size 3, 2.74mm



Connector & Housing Type: Plug
Connector System: Board-to-Board

Number of Positions: 25

Centerline (Pitch): 2.74 mm [ .108 in ]

Number of Rows: 2

All D-Sub Plug Assembly: Standard, Right Angle, Shell Size 3, 2.74mm (39)

## **Features**

# **Product Type Features**

Grounding Indents	With
Grounded	Yes
Grounding Straps	Without
Footprint	13.84 mm[.545 in]
Shell Type	Full Metal Shell
Connector & Housing Type	Plug
Connector System	Board-to-Board
D-Sub Shell Size	3
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Product Type	Connector

## **Configuration Features**

Number of Positions	25
Number of Rows	2
PCB Mount Orientation	Right Angle
Preloaded	Yes



# **Body Features**

Female Screwlock Material	Steel
Plastic	No
Insert Material	Brass
Female Screwlock Plating Material	Zinc
Connector Profile	Standard
Connector Profile  Shell Plating Material	Standard Tin

### **Contact Features**

Contact Mating Area Plating Material	Gold
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Brass
Contact Shape & Form	Square
Contact Current Rating (Max)	6 A
	30 μin

# **Termination Features**

Grounding Clips	Without
Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Post Length	3.18 mm[.125 in]

# Mechanical Attachment

Panel Mount Feature	Without
PCB Mount Retention	With
PCB Mount Retention Type	Mounting Hole
Mating Retention	With
Mating Retention Type	Female Screwlocks, 4-40 UNC
Connector Mounting Type	Board Mount
Mounting Hole Diameter	3.05 mm[.12 in]

# **Housing Features**

Centerline (Pitch)	2.74 mm[.108 in]
Housing Material	Nylon GF, PBT GF



Housing Color	Black
Dimensions	
Row-to-Row Spacing	2.84 mm[.112 in]
PCB Thickness (Recommended)	2.36 mm[.093 in]
Usage Conditions	
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Operation/Application	
Circuit Application	Signal
Industry Standards	
Insert Flammability Rating	UL 94V-0
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Method	Package
Packaging Quantity	70
Other	
Comment	Plugs are preloaded with size 20 DF posted pin contacts

# **Product Compliance**

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Pb (.35% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C



#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

# Compatible Parts



TE Part # CAT-AM7-248H5
IDC D-Sub: Receptacle Assembly,
Wire to Wire, Signal, 2.77 mm



TE Part # CAT-AM7-253 IDC D-Sub: Receptacle Assembly, Low Profile, Signal, 2.77 mm




TE Part # CAT-AM7-248H6 IDC D-Sub: Receptacle Kit, Wire to Wire, Signal, 2.74 mm



TE Part # CAT-AM7-248H9
IDC D-Sub: Receptacle Kit, Cable to
Cable, Signal, 2.77 mm


# Also in the Series | AMPLIMITE HDP



D-Sub Connector Contacts(6)



# Customers Also Bought























## **Documents**

# Product Drawings 25 PLUG RA/MS STD (SL)

English

## **CAD Files**

3D PDF

English

**Customer View Model** 

ENG\_CVM\_5747022-2\_A.2d\_dxf.zip

English

**Customer View Model** 

ENG\_CVM\_5747022-2\_A.3d\_igs.zip

English

**Customer View Model** 

ENG\_CVM\_5747022-2\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

# Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Right-Angle Posted Connectors

English

# **Product Specifications**

**Application Specification** 

English

**Application Specification** 

English

AMPLIMITE HDP, PCB D-Sub Connectors, Plug, Board-to-Board, 25 Position, 2.74mm [.108in] Centerline, 2 Row, Row-to-Row Spacing 2.84 mm [.112 in]



**Instruction Sheets** 

Instruction Sheet (U.S.)

English

Agency Approvals

**UL Report** 

English