




Connectors > D-Shaped Connectors > D-Sub Connectors > Crimp D-Sub Connectors



Connector & Housing Type: **Receptacle**
Connector System: **Cable-to-Cable**
Number of Positions: **9**
D-Sub Shell Size: **1**
Mating Retention: **Without**

Features

Product Type Features

Grade	Standard
Grounding Indents	Without
Product Type	Connector
Shell Type	All Plastic
Connector & Housing Type	Receptacle
Connector System	Cable-to-Cable
D-Sub Shell Size	1
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	9
---------------------	---

Mechanical Attachment

Mating Retention	Without
------------------	---------

Housing Features

Housing Material	Thermoplastic
Housing Color	Black
Centerline (Pitch)	2.74 mm[.108 in]

Usage Conditions



Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

For Use With	Size 20 Crimp Snap-in Contacts
Shielded	Yes
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-035-DCPPS201

D-Sub Crimp: Plug, Signal, 9 Posn, Pin Size 20, Shell Size 1

TE Part # 2198617-9

Ni Plated Plastic Backshell, 9 Way, Str

TE Part # 1393738-2

V42254A6000G115=SUB D GEHAEUSE

TE Part # 206509-1

SIZE 20 KEYING PLUG

Customers Also Bought

TE Part #1658611-4

IDC D-Sub: Plug Assembly, Low Profile, Signal, 2.77 mm

TE Part #1-66504-0

D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20

TE Part #1-487545-7

FFC Receptacle Housing: 1.27mm

TE Part #1-1775469-0

AMP HPI 2.0MM HEADERS

TE Part #1-440129-0

AMP HPI 2.0MM RECEPTACLE HOUSINGS

TE Part #1734366-1

Std USB Type A, VT, T/H

TE Part #1-640383-2

12P MTA156 HDR ASSY STR SQ SN

TE Part #1-1879208-6

CPF 0402 43R 0.1% 25PPM 1K RL

TE Part #91525-1

CCII AMPLIMITE HDP-20 PIN SKT 26-22 ASSY

Documents

Product Drawings

9 CONTACT HSG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_207752-3_H.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_207752-3_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_207752-3_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English