




Connectors > D-Shaped Connectors > D-Sub Connectors > PCB D-Sub Connectors



Connector & Housing Type: **Receptacle**
Connector System: **Cable-to-Cable**
Number of Positions: **15**
Centerline (Pitch): **2.28 mm [.089 in]**
Number of Rows: **3**

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Cable-to-Cable
D-Sub Shell Size	1
Sealable	No

Configuration Features

Number of Positions	15
Number of Rows	3

Body Features

Connector Profile	Standard
-------------------	----------

Contact Features

Contact Shape & Form	Round
----------------------	-------

Mechanical Attachment

Mating Retention	Without
------------------	---------



Housing Features

Centerline (Pitch)	2.28 mm[.089 in]
--------------------	------------------

Dimensions

Row-to-Row Spacing	1.98 mm[.078 in]
--------------------	------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






TE Part # CAT-038-DCPPS221
D-Sub Crimp: Plug, Signal, 50 Posn,
Pin Size 22, Shell Size 1



TE Part # 2198617-9
Ni Plated Plastic Backshell, 9 Way, Str



TE Part # 1393738-2
V42254A6000G115=SUB D GEHAEUSE

Customers Also Bought



TE Part #1-917484-5
DYNAMIC 3000 CONTACT



TE Part #1-1437719-1
T01-0540-P03-MALE PLUG
CONNECTOR-CRIMP




TE Part #1-1437719-2
T01-0540-P05-MALE PLUG
CONNECTOR-CRIMP



TE Part #926886-3
UNIV.M-N-L.PIN



TE Part #1-1437719-4
T01-0540-S05-FEMALE PLUG
CONNECTOR-CRIMP



TE Part #1393738-1
V42254A6000G109=SUB D GEHAEUSE

TE Part #1108782-2
MDL2-GR.U-6.B1-3

TE Part #1103018-2
MDL2.3+4.BU.C



TE Part #1103017-1
MDL2.HN.D.15.STI.C

Documents

Product Drawings
15P.HDP22 REC.ASSY.

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_216164-1_D.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_216164-1_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_216164-1_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Ocena wizualna zlaczy HD20 WTW](#)

[Workmanship Specification](#)