

1757829-1 ✓ ACTIVE

AMPLIMITE

TE Internal #: 1757829-1

Box Mount D-Sub Connectors, Plug, Post Diameter .76 mm [.03 in],
Vertical, Cable-to-Board, 9 Position, 1 D-Sub Shell Size, Pin, 20 D-
Sub Contact Size

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connectors > Box Mount D-Sub Connectors



Connector & Housing Type: **Plug**

Post Diameter: **.76 mm [.03 in]**

PCB Mount Orientation: **Vertical**

Connector System: **Cable-to-Board**

Number of Positions: **9**

Features

Product Type Features

Product Type	Connector
Connector & Housing Type	Plug
Connector System	Cable-to-Board
D-Sub Shell Size	1
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Blindmate	No

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	9
Power/Signal/Coax Combination	No

Body Features

Box Mount D-Sub Connector Insert Arrangement	MS18273-1
Shell Plating Material	Zinc
Shell Material	Steel
Non-Magnetic	No

Contact Features

Contact Type	Pin
--------------	-----



Contact Mating Area Plating Material	Gold
Contact Base Material	Brass or Beryllium Copper
D-Sub Contact Size	20
Contact Current Rating (Max)	5 A

Termination Features

Termination Post Length	4.78 mm[.188 in]
-------------------------	------------------

Mechanical Attachment

Mounting Hole Diameter	3.05 mm[.12 in]
------------------------	-----------------

Housing Features

Centerline (Pitch)	2.77 mm[.109 in]
--------------------	------------------

Dimensions

Post Diameter	.76 mm[.03 in]
---------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

ULTRA-LITE Connector	No
Circuit Application	Signal

Industry Standards

NASA Qualification	No
--------------------	----

Packaging Features

Packaging Method	Package
------------------	---------

Other

Comment	"Z" is stamped on connectors following M24308 part number as required. "Z" designates zinc shell plating., For solder dip product see part number 1757829-6.
---------	--

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021
(211)

Candidate List Declared Against: JAN 2021
(211)

SVHC > Threshold:

Pb (3.7% in Contact/Component)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1757819-5
AMPLIMITE,ASY,PLUG,STD,109,ZN,5



TE Part #1757820-4
AMPLIMITE,ASY,RCPT,STD,109,ZN,4



TE Part #1676143-3
RN 0805 100R 0.1% 10PPM 5KRL



TE Part #1-1617754-7
FCA-410-1620M=M83536/16-020M



TE Part #1734595-8
AMP HPI 1.0MM HEADERS




TE Part #1218125-3
25 POS,ASSY,PLUG,LOW PROF,109



TE Part #1757827-2
AMPLIMITE,PLUG ASY,POSTD,109,ZN,2



TE Part #1676343-2
RN 0805 44K2 0.1% 10PPM 1KRL



TE Part #1757829-3
AMPLIMITE, PLUG ASY, POSTD, 109, ZN,
3



TE Part #YDIV44E15-35SNC009
RECP ASSY

Documents

Product Drawings

[AMPLIMITE, PLUG ASY, POSTD, 109, ZN, 1](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1757829-1_E.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1757829-1_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1757829-1_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

[UL Report](#)

English