



Connectors > RF Coax Connectors > RF Adapters > In-Series Adapters



RF Connector Type: **N Series**

Body Angle: **Straight**

RF Connector Center Contact Material: **Beryllium Copper**

RF Connector Center Contact Plating Material: **Gold (Au)**

Impedance: **50 Ω**

Features

Product Type Features

RF Connector Type	N Series
Connector System	Cable-to-Cable
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Impedance	50 Ω
-----------	------

Signal Characteristics

Frequency	18 GHz
-----------	--------

Body Features

Body Angle	Straight
------------	----------

Contact Features

RF Connector Center Contact Material	Beryllium Copper
--------------------------------------	------------------



RF Connector Center Contact Plating Material

Gold (Au)

Usage Conditions

Operating Temperature Range

-55 – 125 °C[-67 – 257 °F]

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Not Yet Reviewed

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021 (211)
 Candidate List Declared Against: JAN 2021 (211)
 SVHC > Threshold:
 Pb (.35% in Component Part)

Article Safe Usage Statements:
 Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1057377-1
3082 2240 00,ADAPTER,N TO SMA



TE Part # 1-2016658-0
N M DOUBLE,18G,1.0M WITH ARMOR,PUR



TE Part # 1-2016703-0
N M TO SMA M,18G,1.0M WITH ARMOR




TE Part # 2081557-1
ADAPTOR N MALE TO 7-16 MALE



TE Part # 2081561-1
ADAPTOR N MALE TO N FEMALE RIGHT ANGLE



TE Part # 1-2016657-0
N M DOUBLE,18G,1.0M WITHOUT ARMOR



TE Part # 1058663-1
3682 0000 02



TE Part # 2081560-1
ADAPTER N MALE TO N MALE ELBOW



TE Part # 1-2016657-5
N M DOUBLE,18G,1.5M WITHOUT ARMOR



TE Part # 1-2016658-5
N M DOUBLE,18G,1.5M WITH ARMOR,PUR



TE Part # 1-2016703-5
N M TO SMA M,18G,1.5M WITH ARMOR



TE Part # 2016657-6
N M DOUBLE,18G,0.6M WITHOUT ARMOR




TE Part # 2016658-6
N M DOUBLE,18G,0.6M WITH ARMOR,PUR



TE Part # 2016703-6
N M TO SMA M,18G,0.6M WITH ARMOR


Customers Also Bought



TE Part #1-87523-6
MOD IV RECP LP






TE Part #102387-1
10 MODIV HSG COMP DR .100 POL



TE Part #1-103309-0
050 LOPRO HDR SP 30DP



TE Part #103309-5
020 LOPRO HDR SP 30DP



Documents

Product Drawings

ADAPTER N FEMALE TO N FEMALE

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2081562-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2081562-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2081562-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English