



Nanonics

TE Internal #: 8-1589473-3

Standard Rectangular Connectors, Connector Assembly, Plug, Mating Alignment, Polarization Mating Alignment Type, Mating Retention

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**

Connector & Housing Type: **Plug**

Mating Alignment: **With**

Mating Alignment Type: **Polarization**

Mating Retention: **With**

Features

Product Type Features

Product Style	Assembly
Shape	Rectangular
Wire/Cable Type	Stranded
Connector Type	Connector Assembly
Housing Type	Plug
Connector Product Type	Connector Assembly
Connector & Housing Type	Plug
Connector System	Cable-to-Cable
Sealable	No

Configuration Features

Number of Cavities	25
Number of Positions	25
Number of Rows	2
Panel Gasket	Without

Electrical Characteristics

Operating Voltage	500 VAC
-------------------	---------

Contact Features

--	--



Contact Layout	Staggered
Contact Type	Pin
Wire Contact Termination Area Plating Material	Gold
Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Gold
Contact Retention Within Housing	Without
Contact Current Rating (Max)	1 A

Mechanical Attachment

Panel Mount	No
Panel Mount Feature	Without
Mating Alignment	With
Mating Alignment Type	Polarization
Mating Retention	With
Mating Retention Type	JackscREW
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Aluminum
Centerline (Pitch)	.64 mm[.025 in]

Dimensions

Wire Size	.05 mm ²
Row-to-Row Spacing	1.02 mm[.04 in]

Usage Conditions

Operating Temperature Range	-200 – 200 °C[-328 – 392 °F]
-----------------------------	------------------------------

Operation/Application

Shielded	No
Circuit Application	Signal

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #EF9981-000
Bulbous Heat Shrink Boots: Lipped, Right Angle



TE Part #1757624-1
SZ 8 COAX PIN, RG142, HEX CRIMP



TE Part #204502-4
RECEPT ASSY, 26 POSN, AMPLIMITE



TE Part #205162-6
AMPLIMITE, ASY, PLUG, 109, 1



TE Part #YACT26MA98SEV00100
Straight Plug D38999, A98 Insert



TE Part #YACT26MG35SCV00100
Straight Plug D38999, G35 Insert



TE Part #2102579-1
ASSY 2 AL COPALUM LITE DUAL HOLE 3/8



TE Part #YACT24MA98SNV00100
JAM NUT RECEPTACLE



TE Part #F78598-000
B-155-1504



TE Part #ZPF00000000163975
DMC-M 99-04 CN (=33537-PC000)

Documents

Product Drawings

[STM025PC2DC012N = WDUALOBE](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_8-1589473-3_S.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_8-1589473-3_S.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_8-1589473-3_S.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1589472 Nanonics Cross Reference](#)

English