



TE Internal #: 5415025-2
RF Connectors, BNC RF Interface, Jack, RF Connector Mated Outer
Diameter (Approximate) .572 in [14.53 mm], 50 Ω, Bayonet, 4GHz
Operating Frequency
[View on TE.com >](#)

Connectors > RF Coax Connectors > RF Connectors > BNC Right Angle M Jack RF Connector, 50 Ohm, Bayonet Coupling Mechanism



RF Interface: **BNC**
RF Connector Style: **Jack**
RF Connector Mated Outer Diameter (Approximate): **14.53 mm [.572 in]**
Impedance: **50 Ω**
RF Connector Coupling Mechanism: **Bayonet**
[All BNC Right Angle M Jack RF Connector, 50 Ohm, Bayonet Coupling Mechanism \(45\)](#)

Features

Product Type Features

RF Interface	BNC
RF Connector Style	Jack
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	1
PCB Mount Orientation	Right Angle
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Insulation	Without
-----------------	---------



Body Material	Zinc
Body Plating Material	Tin

Contact Features

RF Connector Center Contact Underplating Material	Nickel
	30 μin
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Phosphor Bronze

Termination Features

Termination Method to Wire & Cable	Crimp
Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Post & Tail Length	4.34 mm[.17 in]

Mechanical Attachment

Panel Attachment Style	Rear Mount
PCB Mount Retention	Without
Panel Mount Feature Type	Lockwasher and Nut
PCB Mount Retention Type	Hold-Down Post
RF Connector Coupling Mechanism	Bayonet
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Mechanical
Detent	With

Dimensions

Mounting Post Length	4.34 mm[.171 in]
RF Connector Mated Outer Diameter (Approximate)	14.53 mm[.572 in]
Height Above PC Board	10.97 mm[.432 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Operating Frequency	4 GHz
---------------------	-------

Packaging Features

Packaging Method	Tray
------------------	------

Other

Grade	Commercial
-------	------------



Additional Features	Hardware Included
Dielectric Material	PTFE

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (4% in Component part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-076-BNCJKISG50
BNC RF Connector: Male (Jack) Assembly, Isolated Ground Protection, 50 Ohm



TE Part # CAT-076-BNCJKSH50
BNC RF Connector: Male (Jack) assembly - short, 50 Ohm, 4Ghz




TE Part # 2-5221128-1
PLUG,COMMERCIAL BNC



TE Part # 5-1634516-1
BNC RM BHJ Hex 50Ohm Nickel Pltd RG58C/U



TE Part # 5227426-1
BNC BLKHD RECPT SEALED




TE Part # 5-1634500-2
BNC Str Plg Hex 50Ohm Nickel Pltd RG58C/



TE Part # 5413959-1
PLUG RTANG BNC HEX 50 OHM



TE Part # 5413959-3
BNC HEX RT ANG PLUG 50 OHM



TE Part # 5413771-3
JACK BLKHD,COML BNC,HEX CRIMP



TE Part # 5227079-5
COMM BNC PLUG



TE Part # 1-5221128-0
PLUG,COMMERCIAL BNC



TE Part # 5228980-5
JACK,BULKHEAD,COM'L,BNC



TE Part # 8-5227079-2
COMM BNC PLUG



TE Part # 5413779-3
COML BNC,50 OHM, HEX CRIMP



TE Part # 5227079-7
COMM. BNC-PLUG



TE Part # 1-5227079-9
COMM BNC PLUG



TE Part # 330876
BNC PLUG



TE Part # 1-221128-0
PLUG,COMMERCIAL BNC



TE Part # 1-5221128-1
PLUG,COMMERCIAL BNC




TE Part # 1-5227079-1
COMM BNC PLUG

Customers Also Bought



TE Part #1735446-4
AMP HPI 2.0MM HEADERS



TE Part #1761608-7
IDC LOW PRO HDR 20P VERT SHT L



TE Part #1888617-1
Cage Assy, QSFP, Through Bezel



TE Part #1676421-1
RN 0805 71K5 0.1% 10PPM CUT LENGTH



TE Part #9-1879512-5
CRGH0805 1% 82R 0.33W

TE Part #1-5747150-6
D-Sub Receptacle Assembly: Vertical,
Shell Size 1, 2.74mm

TE Part #1-2176373-1
RQ 0805 12R7 0.1% 10PPM 1K RL

TE Part #1-9711111-3
10W FRC MADISON SPEC 100-4703
REV. 7

TE Part #1768021-1
IKC02

TE Part #2-1969540-4
HOUSING, PLUG, 24P,DUAL ROW,
EP2.5

Documents

Product Drawings
JACK, RTANG, PCB, 50 OHM, BNC
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_5415025-2_A.3d_igs.zip
English
Customer View Model
ENG_CVM_5415025-2_A.3d_stp.zip
English
Customer View Model
ENG_CVM_5415025-2_A.2d_dxf.zip
English
3D PDF
English
Customer View Model
ENG_CVM_CVM_5415025-2_B.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_5415025-2_B.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_5415025-2_B.3d_stp.zip
English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BNC Connectors

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English