




TE Internal #: 5227222-6

RF Connectors, BNC RF Interface, Jack, RF Connector Mated Outer Diameter (Approximate) .572 in [14.53 mm], 50 Ω, Bayonet, 4GHz

Operating Frequency

[View on TE.com >](#)

Connectors > RF Coax Connectors > RF Connectors > BNC Vertical Male (Jack) RF Connector, 50 Ohm, Bayonet Coupling Mechanism



RF Interface: **BNC**

RF Connector Style: **Jack**

RF Connector Mated Outer Diameter (Approximate): **14.53 mm [.572 in]**

Impedance: **50 Ω**

RF Connector Coupling Mechanism: **Bayonet**

[All BNC Vertical Male \(Jack\) RF Connector, 50 Ohm, Bayonet Coupling Mechanism \(32\)](#)

Features

Product Type Features

RF Interface	BNC
RF Connector Style	Jack
Connector System	Cable-to-Board, Cable-to-Panel
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	1
PCB Mount Orientation	Vertical
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Insulation	Without
-----------------	---------



Body Material	Polyester, PBT
Body Material Finish	Passivated
Body Plating Material	Nickel

Contact Features

RF Connector Center Contact Underplating Material	Nickel
	889 μin
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Phosphor Bronze

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Post & Tail Length	5.33 mm[.21 in]

Mechanical Attachment

Panel Attachment Style	Rear Mount
PCB Mount Retention	With
RF Connector Coupling Mechanism	Bayonet
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Mechanical
Detent	With

Housing Features

Housing Color	Black
---------------	-------

Dimensions

Mounting Post Length	3.48 mm[.137 in]
RF Connector Mated Outer Diameter (Approximate)	14.53 mm[.572 in]
Height Above PC Board	34.93 mm[1.375 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Operating Frequency	4 GHz
---------------------	-------

Packaging Features

Packaging Method	Tube
------------------	------

Other

--	--



Grade	Commercial
Comment	If an Insulating Bushing is required, see Part Number 330620., Lockwasher and Jam Nut must be ordered separately.
Dielectric Material	Polymethylpentene

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-076-BNCJKSH50
BNC RF Connector: Male (Jack)
assembly - short, 50 Ohm, 4Ghz



TE Part # 5-1634516-1
BNC RM BHJ Hex 50Ohm Nickel Pltd
RG58C/U



TE Part # 5227426-1
BNC BLKHD RECPT SEALED



TE Part # 5413771-3
JACK BLKHD,COML BNC,HEX CRIMP



TE Part # 5227079-5
COMM BNC PLUG



TE Part # 1-5221128-0
PLUG,COMMERCIAL BNC



TE Part # 5228980-5
JACK,BULKHEAD,COM'L,BNC



TE Part # 8-5227079-2
COMM BNC PLUG



TE Part # 5413779-3
COML BNC,50 OHM, HEX CRIMP



TE Part # 5227079-7
COMM. BNC-PLUG



TE Part # 1-5227079-9
COMM BNC PLUG




TE Part # 330876
BNC PLUG



TE Part # 1-5221128-1
PLUG,COMMERCIAL BNC



TE Part # 1-5227079-1
COMM BNC PLUG



TE Part # 227079-6
COMM. BNC-PLUG



TE Part # 5227079-9
COMM. BNC-PLUG



TE Part # 5227169-5
BNC - SOLDER RECEPT



TE Part # 5227169-7
BNC SOLDER JACK RECEPTACLE



TE Part # 5227169-8
BNC - SOLDER RECEPT



TE Part # 5227716-3
BNC SOLDER RECEPT JACK

Customers Also Bought





TE Part #1-2176070-7
SMD Power Resistor: 2 Watt, 3521 Series



TE Part #1-87215-0
02 MODII HDR DRST UNSHRD .100



TE Part #1658526-8
609-1430LF FEM SOCKET, LEAD FREE



TE Part #1879208-8
CPF 0402 20R 0.1% 25PPM 1K RL



TE Part #1-329632-2
LOCKWASHER, PLATED




TE Part #1-2176092-8
RP 2A 0.25W 1K0 0.1% 25PPM 1K RL



TE Part #8-1625868-5
RP 2A 0.25W 40R2 0.1% 25PPM 1K RL



TE Part #1609112-8
CORCOM C SERIES IEC UNFILTERED INLETS



TE Part #1-329631-2
JAM NUT, PLATED



TE Part #1-2834015-3
3POS 2.54MM TES CONN.

Documents

Product Drawings

VERT JK W/MTG PINS, BNC PCB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5227222-6_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5227222-6_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5227222-6_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



BNC Connectors

English

Product Specifications

Product Specification

English

Product Specification

English

Product Environmental Compliance

MD_5227222-6_07032014856_dmtec

English

MD_5227222-6_07032014856_dmtec

English

Instruction Sheets

Instruction Sheet (U.S.)

English