




Connectors > RF Coax Connectors > RF Connectors > SMB Connector: Female (Plug), Mated Outer Dia. 4.75mm, 50 Ohm



RF Interface: **SMB**

RF Connector Style: **Plug**

RF Connector Mated Outer Diameter (Approximate): **4.75 mm [.187 in]**

Impedance: **50 Ω, 75 Ω**

Compatible With RF Cable Type: **RG 174, RG 188, RG 316**

[All SMB Connector: Female \(Plug\), Mated Outer Dia. 4.75mm, 50 Ohm \(32\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
RF Interface	SMB
RF Connector Style	Plug
Compatible With RF Cable Type	RG 174, RG 188, RG 316
Connector System	Cable-to-Cable
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω, 75 Ω
-----------	------------

Body Features

--	--



Cable Connector Orientation	Right Angle
Body Material	Brass
Body Plating Material	Nickel
Body Underplating Material	Copper

Contact Features

RF Connector Center Contact Underplating Material	Nickel
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Beryllium Copper

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

RF Connector Coupling Mechanism	Snap-Fit
RF Contact Captivation Method	Mechanical
Detent	With

Dimensions

RF Connector Mated Outer Diameter (Approximate)	4.75 mm[.187 in]
---	------------------

Usage Conditions

Operating Temperature Range	-65 – 85 °C[-85 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Operating Frequency	4 GHz
---------------------	-------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

Grade	Mil-Type
Outer Contact Plating Material	Gold over Nickel
Dielectric Material	PTFE

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-884-SMBF50 SMB Connector: Female (Plug), Mated Outer Dia. 4.75mm, 50 Ohm	TE Part # CAT-884-SMBV50 SMB Connector: Male (Jack), Vertical Mount, Mated Outer Dia. 4.75mm, 50 Ohm	TE Part # CAT-884-SMBMRA50 SMB Connector: Male (Jack), Right-angle Mount, Mated Outer Dia. 4.75 mm	TE Part # CAT-884-SMBFRA50 SMB Connector: Female (Plug), Right-Angle Mount, Mated Outer Dia. 4.75 mm
TE Part # CAT-884-SMBM50 SMB Connector: Male (Jack), Mated Outer Dia. 4.75mm, 50 Ohm	TE Part # 228553-1 SMB COMML BLKHD ADAPTER	TE Part # CAT-884-SMBMSF50 SMB RF Connector: Male (Jack), Snap Fit, 50 Ohm	TE Part # 58483-1 TRIPLE HEX DIE ASSY SMB



Customers Also Bought



Documents

Product Drawings
PLUG,CABLE,RTANG,SMB,NI PLTD
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_414002-3_K.2d_dxf.zip

414002-3

RF Connectors, SMB RF Interface, Plug, RF Connector Mated Outer Diameter
(Approximate) .187 in [4.75 mm], 50 Ω / 75 Ω



English

Customer View Model

[ENG_CVM_CVM_414002-3_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_414002-3_K.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SMB Connectors](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English