



AMP SMA

TE Internal #: 3-1478978-1

AMP SMA, RF Connectors, SMA RF Interface, Receptacle, RF Connector Mated Outer Diameter (Approximate) .25 in [6.35 mm], 50 Ω, Screw

[View on TE.com >](#)

Connectors > RF Coax Connectors > RF Connectors



RF Interface: **SMA**
RF Connector Style: **Receptacle**
RF Connector Mated Outer Diameter (Approximate): **6.35 mm [.25 in]**
Impedance: **50 Ω**
RF Connector Coupling Mechanism: **Screw**

Features

Product Type Features

Connector Product Type	Connector Assembly
RF Interface	SMA
RF Connector Style	Receptacle
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	1
PCB Mount Orientation	Right Angle
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Material	Brass
---------------	-------



Body Plating Material	Gold
-----------------------	------

Contact Features

RF Connector Center Contact Underplating Material	Copper
RF Connector Contact Configuration	Not Captivated
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Phosphor Bronze

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Post & Tail Length	3.4 mm[.133 in]

Mechanical Attachment

RF Connector Coupling Mechanism	Screw
Connector Mounting Type	Board Mount
RF Contact Captivation Method	Mechanical
Detent	Without

Dimensions

Panel Cutout	1 x 1.4 + 4 x 1.5
Product Length	13.5 mm[.532 in]
RF Connector Mated Outer Diameter (Approximate)	6.35 mm[.25 in]
Height Above PC Board	10.1 mm[.397 in]

Usage Conditions

Operating Temperature Range	-65 – 165 °C[-85 – 329 °F]
-----------------------------	----------------------------

Operation/Application

Operating Frequency	6 GHz
---------------------	-------

Packaging Features

Packaging Quantity	30
Packaging Method	Bag

Other

Grade	Commercial
Dielectric Material	Delrin

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.6% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1056443-1
[2831 7388 02](#)



TE Part # 1052067-1
[2037 5006 02,SMA RA CABLE PLUG](#)



TE Part # 1052076-1
[2037 5008 02](#)



TE Part # 1050721-1
[2001 7188 02](#)





TE Part # 1056462-1
2837 7388 02



TE Part # 1051664-1
2031 5012 00

Also in the Series | AMP SMA



Battery Holders(1)



Between Series Adapters(3)



Coax Contacts(1)



Coax Terminators(1)



In-Series Adapters(35)



Rack & Panel Ferrules & Inserts(1)



RF Cable Assemblies(2)



RF Connector Hardware(2)



RF Connector Launchers(13)



RF Connector Shrouds(10)



RF Connectors(527)

Customers Also Bought




TE Part #1-1634817-0
BNC / TNC Lockwasher



TE Part #1622367-1
LR1 1% 1M0



TE Part #1571983-4
GDH04S04=DIP SWITCH



TE Part #1-1337463-0
BNC Plg Term 50Ohm Silver Pltd






TE Part #1-1478979-0
SMA STR PCB SKT GSS



TE Part #9-2176091-7
RP 2A 0.25W 604R 0.1% 25PPM 1K RL



TE Part #1-1761465-2
PCI Express RA assy 5.8mm slot 2.3 mm pc



TE Part #1-826648-0
10P AMPMODU II STIFT LEI



TE Part #1513634-1
400411LF Molded Stamped Antenna



TE Part #1-1337482-0
SMB Str PCB Skt 50Ohm Gold Plt

Documents

Product Drawings

SMA R/A PCB SKT GB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1478978-1_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1478978-1_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1478978-1_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

MD_3-1478978-1_05102012814

English

MD_3-1478978-1_05102012814

English