



Connectors > RF Coax Connectors > RF Connectors



RF Interface: **QMA**

RF Connector Style: **Plug**

RF Connector Mated Outer Diameter (Approximate): **7.62 mm [.3 in]**

Impedance: **50 Ω**

Compatible With RF Cable Type: **RG 402 Semi-Rigid**

Features

Product Type Features

Connector Product Type	Connector Assembly
RF Interface	QMA
RF Connector Style	Plug
Compatible With RF Cable Type	RG 402 Semi-Rigid
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Cable Connector Orientation	Straight
Body Material	Brass
Body Plating Material	Gold

Contact Features

RF Connector Center Contact Underplating Material	Nickel
---	--------



RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Brass

Termination Features

Termination Method to Wire & Cable	Solder
------------------------------------	--------

Mechanical Attachment

RF Connector Coupling Mechanism	Screw
Connector Mounting Type	Cable Mount (Free-Hanging)
RF Contact Captivation Method	Mechanical
Detent	Without

Dimensions

Product Length	20.5 mm[.807 in]
RF Connector Mated Outer Diameter (Approximate)	7.62 mm[.3 in]

Usage Conditions

Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]
-----------------------------	---------------------------

Operation/Application

Operating Frequency	6 GHz
---------------------	-------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

Dielectric Material	PTFE
---------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.



Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1408332-1 QMA STRAIGHT PWB JACK	 TE Part # 1408341-1 QMA 4 HOLE FLANGE MT JACK - ST	 TE Part # 1408343-1 BSA, QMA JACK TO SMA PLUG ADAP	 TE Part # 1408337-1 QMA RIGHT ANGLE PWB JACK
 TE Part # 1408349-1 QMA BULKHEAD CABLE JACK, .141	 TE Part # 1408340-1 QMA PANEL MT (SCREW-IN) JACK-S	 TE Part # 1408348-1 QMA STRAIGHT CABLE JACK, .141	 TE Part # 1408463-1 QMA RT ANGLE SURF MNT JACK
 TE Part # 619215-1 QMA PRESS IN JACK	 TE Part # 2016027-1 QMA EDGE LAUNCH JACK		

Also in the Series | AMP SMA



Battery Holders(1)	Between Series Adapters(3)	Coax Contacts(1)	Coax Terminators(1)
In-Series Adapters(35)	Rack & Panel Ferrules & Inserts(1)	RF Cable Assemblies(2)	RF Connector Hardware(2)
RF Connector Launchers(13)	RF Connector Shrouds(10)	RF Connectors(527)	

Customers Also Bought

TE Part #140814-2 250 FASTON,TAB,TPBR	TE Part #34150 PG R 22-16 COMM 22-18 MIL 1/4	TE Part #4-1393767-4 R10-E2Z4-V15.0K=R10	TE Part #1408347-1 QMA RT ANGLE CABLE PLUG, .141
TE Part #3-1445053-2 MICRO MNL HDR ASSY S/ROW LF	TE Part #104351-3 06 MODII HDR DRST B/A W/HD	TE Part #3-644463-3 03P MTA156 CONN ASSY 22AWG RED	TE Part #2162513001 55A0111-12-3



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1408346-1_D_c-1408346-1-d.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1408346-1_D_c-1408346-1-d.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1408346-1_D_c-1408346-1-d.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

QMA Connectors

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English