



Connectors > RF Coax Connectors > Coax Terminators



Impedance: 50 Ω

Sealable: No

Circuit Application: Signal

Operating Temperature Range: -65 – 165 °C [-85 – 329 °F]

## Features

### Product Type Features

Product Type	Terminator
Grade	Professional
Sealable	No

### Configuration Features

Tether	Without
--------	---------

### Electrical Characteristics

Resistor Specification	.5 ±2% W
Impedance	50 Ω

### Signal Characteristics

Frequency	1 GHz
-----------	-------

### Body Features

Body Style	Straight
Body Insulation	With
Body Material	Brass
Body Plating Material	Silver



### Contact Features

RF Connector Center Contact Plating Material	Silver
RF Connector Center Contact Material	Brass

### Usage Conditions

Operating Temperature Range	-65 – 165 °C[-85 – 329 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	Signal
---------------------	--------

### Packaging Features

Packaging Quantity	50
Packaging Method	Tray

### Other

Gasket Material	Silicone Rubber
-----------------	-----------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.35% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 6-1337458-0  
BNC T Adpt JPJ 50Ohm Nickel Gold Pltd



TE Part # 131228-2  
BNC TYPE E PANEL JACK ASSEMBLY



TE Part # 6-1337433-0  
BNC RM BHj Hex 50Ohm Nickel Pltd RG58C/U



TE Part # 6-1337434-0  
BNC RM BHJ Hex 50Ohm Silver Pltd RG58C/U



TE Part # 6-1337441-0  
BNC Str Jk Hex 50Ohm Nickel Pltd RG58C/U



TE Part # 6-1337442-0  
BNC Str Jk Hex 50Ohm Silver Pltd RG58C/U



TE Part # 6-1337445-0  
BNC Str PCB Skt 50Ohm Silver Pltd



TE Part # 6-1337446-0  
BNC Pnl Skt 50Ohm Silver Pltd



TE Part # 6-1337447-0  
BNC Ins BHSkt 50Ohm Nickel Silver Pltd




TE Part # 6-1337448-0  
BNC BHSkt + TAG 50Ohm Nickel Pltd



TE Part # 6-1337449-0  
BNC BHSkt 50Ohm Nickel Pltd



TE Part # 6-1337450-0  
BNC BHSkt + TAG 50Ohm Silver Pltd



TE Part # 6-1337451-0  
BNC BHSkt 50Ohm Silver Pltd





TE Part # 6-1337452-0  
BNC Ins BHSkt 50Ohm Nickel Gold Pltd



TE Part # 6-1337535-0  
BNC Str PCB Skt 50Ohm Nickel Pltd



TE Part # 6-1337536-0  
BNC Str Jk MC 50Ohm Nickel Pltd RG58C/U,



## Customers Also Bought



## Documents

### Product Drawings

BNC Plg Term 50Ohm Silver Pltd

English

### CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-1337463-0\_D.2d\_dxf.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-1337463-0\\_D.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-1337463-0\\_D.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

## Datasheets & Catalog Pages

[BNC Connectors](#)

English