



TE Internal #: 1-1337562-0

Between Series Adapters, Side A Interface FME, Side A Gender Plug, Side B Interface BNC, Side B Gender Plug, 50 Ω, Wire-to-Wire, 1 Position

[View on TE.com >](#)

Connectors > RF Coax Connectors > RF Adapters > Between Series Adapters



Side A Interface: **FME**

Side A Gender: **Plug**

Side B Interface: **BNC**

Side B Gender: **Plug**

Impedance: **50 Ω**

Features

Product Type Features

Side A Interface	FME
Side A Gender	Plug
Side B Interface	BNC
Side B Gender	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Impedance	50 Ω
-----------	------

Signal Characteristics

Frequency	2 GHz
-----------	-------

Body Features

--	--



Body Material	Brass
Body Style	Straight
Material	Brass
Body Plating Material	Nickel

Contact Features

RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Brass

Mechanical Attachment

Coupling Nut Plating Material	Nickel
Connector Mounting Type	Bulkhead

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]
-----------------------------	---

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 6-1337552-0
FME Str Jk Hex Nickel Pltd RG58C/U, 141A

Customers Also Bought

TE Part #1658615-4
IDC D-Sub: Plug Assembly, Low Profile, Signal, 2.77 mm

TE Part #1658614-4
IDC D-Sub: Receptacle Assembly, Low Profile, Signal, 2.77 mm

TE Part #2204456-1
MULTI-BEAM HD R/A PLUG 4VP+20S SOLDER

TE Part #165615-2
110 PIDG FASTON REC

TE Part #2-1377174-3
SMP 0-0320570-0

TE Part #1-86177-5
16 MODIV HSG COMP DR .100CL

TE Part #DT06-2S
DEUTSCH DT Series Housings & Connectors

TE Part #1768019-3
EET-3774P-9

TE Part #2204416-1
MULTI-BEAM HD R/A.REC.4VP+20S SOLDER

TE Part #2-1437468-8
SCCLA012XXACXA=1/30SEC01TIMER

Documents

Product Drawings
FME Str Plg-BNCP Adp Nickel Pltd
English



CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-1337562-0_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1337562-0_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1337562-0_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RF Between Series Adapters

English