




Connectors > RF Coax Connectors > Coax Contacts



Connector System: **Cable-to-Board**
Sealable: **No**
Connector & Contact Terminates To: **Printed Circuit Board**
PCB Mount Orientation: **Straight**
Contact Type: **Pin**

Features

Product Type Features

Product Type	Contact
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Compatible With RF Cable Type	Coaxial

Configuration Features

PCB Mount Orientation	Straight
-----------------------	----------

Body Features

Body Angle	Straight
------------	----------

Contact Features

RF Connector Center Contact Material	Iron-Nickel Alloy
Contact Type	Pin
RF Connector Center Contact Plating Material	Gold
Contact Mating Retention	Without

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Usage Conditions

Operating Temperature Range	-65 – 165 °C[-85 – 329 °F]
-----------------------------	----------------------------



Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | AMP SMA



Battery Holders(1)



Between Series Adapters(3)



Coax Contacts(1)



Coax Terminators(1)



In-Series Adapters(35)



Rack & Panel Ferrules & Inserts(1)



RF Cable Assemblies(2)



RF Connector Hardware(2)



RF Connector Launchers(13)




RF Connector Shrouds(10)



RF Connectors(527)

Customers Also Bought




TE Part #2176407-1
3560 13K 1%



TE Part #7-2176306-5
RP 1E 0.1W 6K81 0.1% 25PPM 5K RL



TE Part #YDTS26F25-20PBV001
D38999: Straight Plug, 25-20 Insert



TE Part #1423795-1
R10-E1W2-S3.2K=R10



TE Part #1958510-1
SPLICE,STRATO-THERM, BUTT, HR, 2
AWG



TE Part #596971-000
22759/43-8-2



TE Part #3-647479-2
02P MTA156 CONN ASSY 18AWG
ORA



TE Part #935487-000
44AM1161-22-MST6-9CS2275



Documents

Product Drawings

[2998 5022 94](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1056728-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1056728-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1056728-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SMP Connectors](#)

English