




TE Internal #: 1060266-1

Between Series Adapters, Side A Interface OSM, Side A Gender Jack, Side B Interface SMC, Side B Gender Jack, Wire-to-Wire, 1 Position, Wire & Cable

[View on TE.com >](#)

Connectors > RF Coax Connectors > RF Adapters > Between Series Adapters



Side A Interface: **OSM**

Side A Gender: **Jack**

Side B Interface: **SMC**

Side B Gender: **Jack**

Connector System: **Wire-to-Wire**

Features

Product Type Features

Side A Interface	OSM
Side A Gender	Jack
Side B Interface	SMC
Side B Gender	Jack
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Body Material	Stainless Steel
Body Style	Straight

Contact Features

RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Beryllium Copper

Mechanical Attachment

Connector Mounting Type	Bulkhead
-------------------------	----------

Operation/Application

--	--



Circuit Application	Power & Signal
Other	
Dielectric Material	PTFE Fluorocarbon

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.6% in Component part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings

5080 2240 00

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1060266-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1060266-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1060266-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[RF Between Series Adapters](#)

English