




TE Internal #: 1057385-1
Between Series Adapters, Side A Interface N, Side A Gender Jack,
Side B Interface SMA, Side B Gender Plug, Wire-to-Wire, 1
Position, Wire & Cable
[View on TE.com >](#)

Connectors > RF Coax Connectors > RF Adapters > Between Series Adapters



Side A Interface: **N**
Side A Gender: **Jack**
Side B Interface: **SMA**
Side B Gender: **Plug**
Connector System: **Wire-to-Wire**

Features

Product Type Features

Side A Interface	N
Side A Gender	Jack
Side B Interface	SMA
Side B Gender	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Body Material	Stainless Steel
Body Style	Straight
Material	Stainless Steel

Contact Features

RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Beryllium Copper

Mechanical Attachment

Coupling Nut Material	Stainless Steel
-----------------------	-----------------



Connector Mounting Type

Bulkhead

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Other

Gasket Material	Silicone Rubber
Dielectric Material	TFE Fluorocarbon

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 1051644-1 2031 5003 02	 TE Part # 1050548-1 2001 5032 02	 TE Part # 1050525-1 2001 5003 02,SMA CABLE PLUG	 TE Part # 1051151-1 2007 7941 02,SMA RA CABLE PLUG
 TE Part # 1051638-1 2031 5002 00	 TE Part # 1052067-1 2037 5006 02,SMA RA CABLE PLUG	 TE Part # 1052076-1 2037 5008 02	 TE Part # 1056456-1 2837 7316 02
 TE Part # 1056462-1 2837 7388 02	 TE Part # 1051157-1 2007 7985 02,SMA RA CABLE PLUG	 TE Part # 2081560-1 ADAPTER N MALE TO N MALE ELBOW	

Customers Also Bought

 TE Part #2176415-9 8W STD M/OX 5% 62R	 TE Part #2-211991-2 RECEPT ASSY,SZ 2,ARINC 600	 TE Part #1617131-8 JMSW-6XM = M39016/11-019M	 TE Part #YDTS24W25-35BBV001 Jam Nut: D38999, 25-35 Insert
 TE Part #1056703-1 SMP Jack-Jack Adapter 2980 5004 62	 TE Part #1045422-1 SSMA R/A Cable Plug 1007 7985 00	 TE Part #1338742-1 SEAT TL.6 ROW,HS3 D BM.60 POS	 TE Part #1888291-1 FPH-0421G=FLXPAC HDR P 04 ST LF



Documents

Product Drawings

3082 2243 00

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1057385-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1057385-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1057385-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RF Between Series Adapters

English