

1052602-1 ✓ ACTIVE

[AMP](#) | [AMP SMA](#)

TE Internal #: 1052602-1

AMP SMA, RF Connectors, SMA RF Interface, Jack, RF Connector


Mated Outer Diameter (Approximate) .354 in [8.99 mm], 50 Ω,

Threaded

[View on TE.com >](#)



Connectors > RF Coax Connectors > RF Connectors



RF Interface: **SMA**

RF Connector Style: **Jack**

RF Connector Mated Outer Diameter (Approximate): **8.99 mm [.354 in]**

Impedance: **50 Ω**

RF Connector Coupling Mechanism: **Threaded**

Features

Product Type Features

Connector Product Type	Connector Assembly
RF Interface	SMA
RF Connector Style	Jack
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board, Wire & Cable
Connector Seal Type	Hermetic

Configuration Features

Number of Positions	1
PCB Mount Orientation	Edge
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Material	Stainless Steel
Body Material Finish	Plated
Body Plating Material	Gold

Contact Features

RF Connector Center Contact Underplating Material	Copper, Nickel
---	----------------



RF Connector Center Contact Plating Material	Gold
--	------

RF Connector Center Contact Material	Beryllium Copper
--------------------------------------	------------------

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Mechanical Attachment

Panel Attachment Style	Front Mount
------------------------	-------------

Panel Mount Feature Type	Flange
--------------------------	--------

RF Connector Coupling Mechanism	Threaded
---------------------------------	----------

Connector Mounting Type	Panel Mount
-------------------------	-------------

RF Contact Captivation Method	Mechanical
-------------------------------	------------

Dimensions

Product Length	12.6 mm [.496 in]
----------------	-------------------

RF Connector Mated Outer Diameter (Approximate)	8.99 mm [.354 in]
---	-------------------

Usage Conditions

Operating Temperature Range	-65 – 165 °C [-85 – 329 °F]
-----------------------------	-----------------------------

Operation/Application

Operating Frequency	18 GHz
---------------------	--------

Packaging Features

Packaging Method	Package
------------------	---------

Other

Comment	Hermetically Sealed, With protective cap.
---------	---

Number of Panel Mounting Holes	4
--------------------------------	---

Dielectric Material	PTFE
---------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC	Compliant with Exemptions
-----------------------------	---------------------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197)
--	--



SVHC > Threshold:
Not Yet Reviewed


Halogen Content Not Yet Reviewed for halogen content

Solder Process Capability Hand solderable with tin/lead solder




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




Also in the Series | AMP SMA





In-Series Adapters(35)



Rack & Panel Ferrules & Inserts(1)



RF Cable Assemblies(2)



RF Connector Hardware(2)



RF Connector Launchers(13)



RF Connector Shrouds(10)



RF Connectors(527)

Customers Also Bought



TE Part #440172-008
9527A1318-9



TE Part #1052958-1
2052 8018 92




TE Part #8-1617755-3
FCA-410-AY3



TE Part #F304643001
VG-95218-T028-C014CK3100



TE Part #1617002-9
B07A235BC1 = B07 10 AMP FULL S



TE Part #2-6437006-3
609-3443LF = PCB IDC P 34 ST .125



TE Part #497675-000
55PC0111-22-0



TE Part #6-1617658-7
FW1201A00=FW FULL SIZE RELAY 2



TE Part #754199-000
MTCR-103-04P



TE Part #5148263001
VG-95218-T028-E011CK3100

Documents



Product Drawings

[2052 3122 00](#)

English

Datasheets & Catalog Pages

[Products for Aerospace and Defense](#)

English