




Push Splice Push Grip

TE Internal #: CR2095-000

Push Splice Push Grip, Splices, Wire Terminator, Splice, 22 – 12AWG Wire Size, Standard, Closed End, Closed Barrel, Standard Wire

[View on TE.com >](#)

Terminals & Splices > Splices



Splice Product Type: **Wire Terminator**

Terminal & Splice Type: **Splice**

Wire Size: **22 – 12 AWG**

Sealable: **No**

Splice Features: **Standard**

Features

Product Type Features

Splice Product Type	Wire Terminator
Sealable	No
Splice Type	Closed End
Serrated	No
Splice Barrel Type	Closed Barrel
Splice Wire/Cable Type	Standard Wire
Insulated	No
Support Style	Non-Insulation Support

Electrical Characteristics

Voltage (Max)	600 VAC
---------------	---------

Body Features

Splice Features	Standard
-----------------	----------

Contact Features

Terminal & Splice Type	Splice
------------------------	--------



Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	22 – 12 AWG
-----------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







TE Part # CR2105-000
CPGI-WC-WG-YW-BULK





TE Part # 2271203-1
2PIN WIRE TO WIRE CONNECTOR





TE Part # CR2092-000
CPGI-WC-CG-YW-BULK

Also in the Series | Push Splice Push Grip



Splices(10)


Customers Also Bought





TE Part #1-770903-0
MINI UMNL PIN 22-18 AWG AU






TE Part #1776293-4
TSB23004DS=EUROPA TERM BLK, 8MM





TE Part #130677
PG 12-10 RING M10





TE Part #1-2176392-1
RQ 1206 169K 0.1% 10PPM 5K RL





TE Part #102241-7
09 MODIV HSG COMP SR .100 POL





TE Part #103688-2
03 MTE RCPT HSG SR PLAIN .100





TE Part #1-104257-2
13 MTE RCPT HSG SR LATCH .100





TE Part #1825096-7
TPA11FGPC004





TE Part #T2040242201-000
HE-024-F





TE Part #1-1337448-0
BNC BHSkt + TAG 50Ohm Nickel Pltd



Documents

Product Drawings

CPGI-WC-PG-4-PORT-BULK

English

Datasheets & Catalog Pages

Push Grip Connectors flyer

English

Push Grip Connectors flyer

Push Grip Connectors flyer (Chinese)

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English