




SPLICE

TE Internal #: 60932-2
SPLICE, Splices, Splice, Splice, 2500 – 4700CMA Wire Size, Steel,
Splice Material Thickness .02 in [.5 mm], 0 Serration
[View on TE.com >](#)

Terminals & Splices > Splices



Splice Product Type: **Splice**
Terminal & Splice Type: **Splice**
Sealable: **No**
Wire Size: **2500 – 4700 CMA**
Splice Material: **Steel**

Features

Product Type Features

Barrel Style	Standard
Splice Product Type	Splice
Sealable	No
Serrated	No
Splice Barrel Type	Open Barrel
Splice Wire/Cable Type	Solid, Stranded
Insulated	No
Support Style	Non - Insulation Support

Configuration Features

Number of Serrations	0
----------------------	---

Body Features

Weight per Piece	.149 g
Plating Material	Tin
Splice Material	Steel



Contact Features

Terminal & Splice Type	Splice
------------------------	--------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	2500 – 4700 CMA
Splice Material Thickness	.5 mm[.02 in]
Splice Overall Length	5.56 mm[.219 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 250 °C[-40 – 482 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	50000
Splice Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>







EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 61300-1 SPLICE IS 10000-16000 .031 TPST	 TE Part # 42627-4 SPLICE 3232-8282 .0198 NPST	 TE Part # 63414-1 SPLICE 9000-16000 .031 TPST	 TE Part # 60933-2 SPLICE 2200-2900 .012 TPST
 TE Part # 41627-1 SPLICE 4000-10000 .025 ST	 TE Part # 61008-1 SPLICE 18-16 AWG .0158 TPST	 TE Part # 160659-2 SPLICE 800-2500 .016 NPST	 TE Part # 2-2150102-1 OCEAN_2.0_Applicator-E-120F
 TE Part # 2-2150102-2 OCEAN_2.0_Applicator-E-120F	 TE Part # 2150102-1 OCEAN_2.0_Applicator-E-120F	 TE Part # 2150102-2 OCEAN_2.0_Applicator-E-120F	 TE Part # 7-2150102-1 OCEAN_2.0_Applicator-E-120F
 TE Part # 7-2150102-2 OCEAN_2.0_Applicator-E-120F	 TE Part # 7-2150102-7 OCEAN_2.0_SPARE_PART_KIT-120F		



Also in the Series

SPLICE

Automotive Terminals(1)

Crimp Wire Pins, Tabs & Ferrules(1)

Splices(66)

Customers Also Bought

TE Part #1443997-1
SEALED FUSE & RELAY BOXES

TE Part #925075-3
4W CIRCULAR MATE-N-LOK PIN HSG
BLK

TE Part #2040594-6
AMPSEAL 16 HOUSINGS

TE Part #3-1747050-1
Glow Wire GRACE INERTIA Plug

TE Part #2098250-1
AMPSEAL 16 CONTACTS

TE Part #1803229-1
CRIMPER, INSULATION O PREMIUM

TE Part #1443996-2
COVER, 60 POS, W/O FUSE HOLDER

TE Part #1217176-1
CLUSTER BLOCK RECT.

TE Part #1-2840575-2
PCON12,TERMINAL,FAM SLD/UNSLD

TE Part #354003-5
CRIMPER, "F"

Documents

Product Drawings

SPLICE 2500-4700 .020 TPST

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_60932-2_S.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_60932-2_S.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_60932-2_S.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English