



Terminals & Splices > Splices



Splice Product Type: **SolderSleeve**

Terminal & Splice Type: **Splice**

Wire Size: **.14 mm²**

Sealable: **No**

Features

Product Type Features

Discrete Wire Type	Stranded
Splice Product Type	SolderSleeve
Sealable	No
Splice Type	Tab Terminal
Serrated	No
Splice Barrel Type	Closed Barrel
Splice Wire/Cable Type	Standard Wire
Insulated	Yes

Body Features

Insulation Sleeve Material	Polyvinylidene Fluoride
Weight per Piece	1 g
Plating Material	Pre-Tin
Insulation Material	Heat Shrink Radiation-Crosslinked Modified Polyvinylidene Fluoride

Contact Features

Terminal & Splice Type	Splice
------------------------	--------

Termination Features

Termination Method	Solder
--------------------	--------

Dimensions

--	--



Inside Diameter (Recovered)	.76 mm[.03 in]
Wire Size	304 – 1000 CMA
Splice Wire Insulation Diameter (Max)	.76 mm[.03 in]
Splice Overall Length	10.16 mm[.4 in]

Usage Conditions

Insulation Requirement	Fully Insulated
Cable Temperature Rating	125 °C
Fluid Resistance	Splash Protection
Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	500
Splice Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (37% in Solder) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # CJ2087-000

[HL2010E-KIT-120V](#)

Customers Also Bought



TE Part #1055070-1

[2088 1230 02](#)



TE Part #2102093-1

[Fortis Zd 2Pr 10Col Vert Cent Mod Assy](#)



TE Part #1676246-1

[RN 0805 1K96 0.1% 10PPM CUT LENGTH](#)



TE Part #259725-000

[TXR40AB00-2012BI](#)



TE Part #130094

[PIDG RING TONGUE TERMINALS](#)



TE Part #1-968851-1

[AMP MCP, RECEPTACLE AND TAB](#)




TE Part #0138090001

[TMS-SCE MILITARY GRADE SLEEVES](#)



TE Part #YDTS32Z23RV0010000

[CAP ASSEMBLY](#)



Documents

Product Drawings

D-136-02

English

Datasheets & Catalog Pages

Raychem Electrical Interconnect Products

English

Product Specifications

Product Specification

English