5229995-2 ✔ ACTIVE


CHAMP | CHAMP Docking Connectors

TE Internal #: 5229995-2

CHAMP Docking Connectors, D-Sub Locking & Mounting, Standoff Mounting Stud, Screw Length .64 in [16.26 mm]

View on TE.com >

Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Standoff Mounting Stud**

Screw Length: **16.26 mm [.64 in]**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Standoff Mounting Stud

Mechanical Attachment

Screw & Hole Thread Size	4-40
Screw Length	16.26 mm[.64 in]

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked.Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 5229996-2
SCREW, PAN HD, CAPTIVE

Also in the Series | CHAMP Docking Connectors



D-Sub Covers(27)



D-Sub Locking & Mounting(31)



Docking Connector Guide Hardware(5)



Docking Connectors(33)



IDC D-Sub Connectors(85)




PCB D-Sub Connectors(1)


Customers Also Bought



TE Part #1-745495-8
IDC D-Sub: Receptacle Assembly, Wire to Wire, Signal, 2.77 mm



TE Part #1-745493-4
IDC D-Sub: Receptacle Assembly, Wire to Wire, Signal, 2.74 mm




TE Part #1879074-5
Power Resistor: Aluminum Housed, 75 Watt



TE Part #154N-005G-RT
MEDIA ISOLATED PRESSURE STOCK LIST




TE Part #1623804-8
Wirewound Resistor: Horizontal Mount




TE Part #1393776-3
V23026D1021B201 *X020



TE Part #1757819-3
AMPLIMITE,ASY,PLUG,STD,109,ZN,3



TE Part #9-2176391-1
RQ 1206 107K 0.1% 10PPM 5K RL



TE Part #104346-1
03 MODII HDR SRST B/A W/HD



TE Part #1658615-3
IDC D-Sub: Plug Assembly, Low Profile, Signal, 2.77 mm

Documents

Product Drawings

STAND-OFF, STUD, MTG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5229995-2_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5229995-2_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5229995-2_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.