



Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Ferrule**

Features

Product Type Features

Grade	Standard
Product Type	Accessory
D-Shaped Connector Accessories	Ferrule

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 543344-1
SAHT FERR ON AMPLIMITE HD-20
ASSY

TE Part # 58237-2
FERR ON AMPLIMITE .422-.490 DIE
SET

Also in the Series | AMPLIMITE Kit

D-Sub Backshells & Clamps(136)

D-Sub Contact Accessories(1)

D-Sub Covers(3)

D-Sub Locking & Mounting(122)

Customers Also Bought

TE Part #1658539-5
D-Sub Connector Contacts: Pin, Brass,
Signal, Size 20

TE Part #1-206322-0
CPC CABLE CLAMPS


TE Part #1056443-1
2831 7388 02

TE Part #1-770252-0
UMN II PIN LP 14-18





TE Part #DTS26F15-15PN
D38999: Straight Plug, 15-15 Insert



TE Part #1633711-5
ANVIL, COMB



TE Part #1633713-3
CRIMPER, WIRE PREMIUM .031



TE Part #1633713-8
CRIMPER, WIRE PREMIUM .033

TE Part #11H1-13-1-C
11H1-13-1-C



TE Part #116677-000
55A1161-24-MST6-9CS2275

Documents

Product Drawings

SHLDNG FERRULE, PLTD, BULK PKG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-747580-1_V.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-747580-1_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-747580-1_V.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Specifications

Application Specification

English



Application Specification

English

Product Environmental Compliance

MD_3-747580-1_04032018058_dmtec

English

MD_3-747580-1_04032018058_dmtec

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Shielding Hardware Kits with AMPLIMITE HD-20 Solder Contact Connectors

English