




Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Ferrule**

Features

Product Type Features

Grade	Standard
Product Type	Accessory
D-Shaped Connector Accessories	Ferrule

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 543344-1 SAHT FERR ON AMPLIMITE HD-20 ASSY	 TE Part # 58449-1 DIE HOLDER ASSY, AMPLIMITE	 TE Part # 948761-3 PINCE FERRULE HDE	 TE Part # 543424-6 AMPLIMITE FERR DIE SET
---	---	---	--

Also in the Series | AMPLIMITE Kit

 D-Sub Backshells & Clamps(136)	 D-Sub Contact Accessories(1)	 D-Sub Covers(3)	 D-Sub Locking & Mounting(122)
---	---	--	--

Customers Also Bought

 TE Part #1658645-1 D-Sub Crimp: Plug, Signal, 9 Posn, Pin Size 20, Shell Size 1	 TE Part #1658648-1 D-Sub Crimp: Plug, Signal, 25 Posn, Pin Size 20, Shell Size 3	 TE Part #1658647-1 D-Sub Crimp: Plug, Signal, 15 Posn, Pin Size 20, Shell Size 2	 TE Part #1658646-1 D-Sub Crimp Recpt Signal 9 Posn, Socket Size 20, Shell Size 1
--	---	---	---



Documents

Product Drawings

SHLDNG FERRULE, PLTD, BULK PKG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-747579-4_W.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-747579-4_W.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-747579-4_W.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Specifications

Application Specification

English

Application Specification

English

Product Environmental Compliance

MD_3-747579-4_04032018058_dmtec

English

MD_3-747579-4_04032018058_dmtec

English



Instruction Sheets

Crimping Die Assemblies f/AMPLIMITE Connectors

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Shielding Hardware Kits with AMPLIMITE HD-20 Solder Contact Connectors

English