




Terminals & Splices > Splices



Splice Product Type: **Splice**
Terminal & Splice Type: **Splice**
Sealable: **No**
Splice Capacity: **1**
Splice Material: **Brass**

Features

Product Type Features

Splice Product Type	Splice
Sealable	No
Splice Type	In-Line Splice
Serrated	No
Splice Accessory Type	Splice
Insulated	Yes

Configuration Features

Splice Capacity	1
-----------------	---

Body Features

Insulation Material	Nylon
Splice Material	Brass

Contact Features

Terminal & Splice Type	Splice
------------------------	--------

Housing Features

Housing Material	Nylon - GF
------------------	------------

Dimensions

Splice Material Thickness	1.77 mm[.07 in]
Splice Overall Length	44.45 mm[1.75 in]



Usage Conditions

Insulation Requirement	Fully Insulated
------------------------	-----------------

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

RU (UL Component Program)	Approved
CSA Certified	No
Government Qualified Splice	No

Packaging Features

Packaging Quantity	1000
Splice Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 696108-1
.187 PIDG FASTON REC.16-14

Also in the Series | FASTON 187

Crimp Terminal Housings(40)

Insertion & Extraction Tools(1)

Joints & Splices(1)

PCB Terminals(48)

Quick Disconnects(222)

Splices(1)

Customers Also Bought

TE Part #1-2834049-4
LIGHT-N-LOK MODULAR LATCHED RECEPTACLES

TE Part #172337-1
MINI UMNL PLUG HOUSING 3P

TE Part #1-350782-9
09P UMNL V0 CAP HSG BLACK

TE Part #1-332454-0
TERMINAL,PIDG PTFE R AU 18-16



TE Part #T4111511041-000
M12 M, 4P GOLD D_CODE S

SHIELDED PG7

TE Part #1-480388-0
03P CMNL PLUG HSG F/H BLK

TE Part #1-480726-0
03P CMNL CAP HSG D/L NAT

TE Part #1-87159-3
14 MODI CRMP S-I HSG SR .156CL

TE Part #2-1393239-9
RT134020

Documents

Product Drawings

.187 INLINE SPLICE ASSY

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_360035-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_360035-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_360035-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

Agency Approval Document

English