



PIDG

TE Internal #: 323994
PIDG, Splices, Splice, Splice, 26 – 22AWG Wire Size, .12 – .24mm²
Wire Size, Standard
[View on TE.com >](#)

Terminals & Splices > Splices > PIDG BUTT SPLICES



Splice Product Type: **Splice**
Terminal & Splice Type: **Splice**
Wire Size: **.12 – .24 mm²**
Sealable: **No**

[All PIDG BUTT SPLICES \(29\)](#)

Features

Product Type Features

Discrete Wire Type	Stranded
Splice Product Type	Splice
Sealable	No
Splice Type	Butt Splice
Serrated	Yes
Splice Accessory Type	Splice
Splice Barrel Type	Closed Barrel
Splice Wire/Cable Type	Regular Wire
Insulated	Yes
Support Style	Insulation Support

Configuration Features

Number of Serrations	8
----------------------	---

Body Features

Insulation Sleeve Material	Copper
----------------------------	--------



Weight per Piece	.411 g
Plating Material	Tin
Insulation Material	Nylon
Splice Features	Standard
Splice Material	Copper
Splice Color	Yellow - Translucent

Contact Features

Class	1 & 2
Contact Plating Material	Tin
Terminal & Splice Type	Splice

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	.238 – .475 kcmil
Splice Wire Insulation Diameter (Max)	2.08 mm[.082 in]
Splice Material Thickness	.38 mm[.015 in]
Splice Overall Length	22.61 mm[.87 in]

Usage Conditions

Insulation Requirement	Fully Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified Splice	Yes
-----------------------------	-----

Packaging Features

Packaging Quantity	50
Splice Packaging Method	Loose Piece

Other

Comment	26-22 splices are 26-24 range in accordance with MIL-T-7928.
Military Category	Yes



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 46121
DAHT PG PIDG 26-22 ASSY



TE Part # 59275
T-HEAD PIDG PG SH 26-20 ASSY



TE Part # 69344
PIDG 26-22 DIE SET

Also in the Series | PIDG



 Compression Connectors(17)	 Crimp Terminal Housings(1)	 Crimp Wire Pins, Tabs & Ferrules(41)	 Knife Disconnects(11)
 PCB Terminals(9)	 Portable Crimp Tools(2)	 Quick Disconnects(53)	 Ring Terminals & Spade Terminals(862)
 Special Purpose Terminals(1)	 Splices(48)		

Customers Also Bought

 TE Part #2-323994-2 PIDG BUTT SPLICES	 TE Part #323914 PIDG RING TONGUE TERMINALS	 TE Part #1757819-8 AMPLIMITE,ASY,PLUG,STD,109,ZN,3,CT	 TE Part #YDTS26W21-16SNV001 D38999: Straight Plug, 21-16 Insert
 TE Part #02291339-000 POWER SUPPLY PSD 40-15 ASSY	 TE Part #10218301-00 QDCC-0300010001: CTO-12000000-07		

Documents



Product Drawings

SPLICE BUTT PIDG 26-24

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_323994_Y.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_323994_Y.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_323994_Y.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PIDG TERMINALS & SPLICES Quick Reference Guide

English

Standard Terminals & Splices

English

PIDG Terminals and Splices Quick Reference Guide

English

Product Specifications

Application Specification

English