




Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: **Ferrule**

Ferrule Type: **Crimp**

Compatible With Connector Shell Size: **5**

Shielded: **Yes**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Ferrule

Body Features

Ferrule Material	Brass
Ferrule Shape	Inner
Ferrule Diameter	19.94 mm[.785 in]
Ferrule Plating Material	Tin-Lead
Ferrule Type	Crimp

Dimensions

Wire Diameter	15.11 mm[.595 in]
	.6 – .65 in

Operation/Application

Compatible With Connector Shell Size	5
Shielded	Yes

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2013 (144) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

TE Part # 543344-1
SAHT FERR ON AMPLIMITE HD-20
ASSY

TE Part # 1-543013-4
DIES AMPLIMITE HD DIE SET

Also in the Series | [AMPLIMITE Kit](#)



D-Sub Backshells & Clamps(136)

D-Sub Contact Accessories(1)

D-Sub Covers(3)

D-Sub Locking & Mounting(122)

Customers Also Bought

TE Part #4-745130-3
SHLDING FERRULE,PLTD,BULK PKG

TE Part #154660-2
FASTON 250 TAB 22-18 AWG TPBR

TE Part #7-745129-5
SHLDING FERRULE,PLTD,BULK PKG

TE Part #5053374026
RNF-3000 Single Wall Stick Heat Shrink

TE Part #1-543013-3
DIES AMPLIMITE HD DIE SET

TE Part #166461-4
IEC-F F.CONT.COSI

TE Part #228979-5
JACK,COML,SERIES BNC,GOLD PL

TE Part #5-87348-8
08 MODII HDR SRST UNSHRD .100

TE Part #543013-8
CRIMPER ANVIL SUBASSY

TE Part #ZPF00000000096054
FDBA 50-22-21 PN-K-A246

Documents

Product Drawings
SHLDING FERRULE,PLTD,BULK PKG
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2-745129-9_AG.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2-745129-9_AG.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-745129-9_AG.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

[CRIMPING DIE ASSEMBLIES 809515-13, -14, -15, AND -16 FOR AMPLIMIT](#)

English

Instruction Sheet (U.S.)

English