




Rail D-Sub Backshells

TE Internal #: 2-2308265-0

Rail D-Sub Backshells, D-Sub Backshells & Clamps, Quick Lock Pins, Shielded, Wire & Cable, Operating Temperature Range -40 – 90 °C [-40 – 194 °F]

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps > QLPIN FOR D-SUB W/ THREADED INSERTS



D-Shaped Connector Accessories: Quick Lock Pins

Shielded: Yes

Connector & Contact Terminates To: Wire & Cable

Operating Temperature Range: -40 – 90 °C [-40 – 194 °F]

All QLPIN FOR D-SUB W/ THREADED INSERTS (10)

Features

Product Type Features

Clam Shell Length	Standard
Grommets	Without
Slide Latch	Without
Product Type	Backshell/Cable Clamp
D-Shaped Connector Accessories	Quick Lock Pins
Connector & Contact Terminates To	Wire & Cable

Mechanical Attachment

Screw & Hole Thread Size	None
--------------------------	------

Usage Conditions

Operating Temperature Range	-40 – 90 °C[-40 – 194 °F]
-----------------------------	---------------------------

Operation/Application

Shielded	Yes
----------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
------------------------------	---------------



EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2308319-1
FULL METAL HOODS SIZE 1 (1)



TE Part # 1-2308321-1
FULL METAL HOODS SIZE 2, (1)



TE Part # 1-2308327-1
FULL METAL HOODS SIZE 3 (1)



TE Part # 1-2308330-1
FULL METAL HOODS SIZE 4 (1)




TE Part # 1-2308338-1
QL-FULL METAL HOODS SIZE 5 (1)
CABLE CLP)


Also in the Series | Rail D-Sub Backshells



Crimp D-Sub Connectors(10)



D-Sub Backshells & Clamps(143)



D-Sub Connector Contacts(5)


Customers Also Bought



TE Part #1-2308265-9
QLPIN FOR D-SUB W/ THREADED INSERTS



TE Part #1-2308298-4
DOUBLE SIDED QLPIN BULKHEAD



TE Part #1-640507-0
02P MR II CAP HSG




TE Part #1-2308327-1
FULL METAL HOODS SIZE 3 (1)




TE Part #1-2176362-0
RQ 0402 49R9 0.1% 10PPM 5K RL




TE Part #1604072-1
Reducing Bushing: 16-0 AWG



TE Part #103944-2
5X3 MTE SHRD PIN SR POL .100



TE Part #1060266-1
5080 2240 00



TE Part #1217029-1
CONTACT AMVAR 125 BLDE 020TPBR



TE Part #ZPF000000000008889
983-6SE 16-24 PN-L

Documents

Product Drawings
QL SET FOR VARIANT B 10
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2-2308265-0_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2-2308265-0_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2308265-0_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Rail D-Sub Backshells Flyer](#)

English