




Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Covers



Connector Cover Type: **Strain Relief**

Number of Positions: **14**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

|                      |               |
|----------------------|---------------|
| Product Type         | Accessory     |
| Connector Cover Type | Strain Relief |

Configuration Features

|                     |    |
|---------------------|----|
| Number of Positions | 14 |
|---------------------|----|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |
|-----------------------------|----------------------------|

Packaging Features

|                    |              |
|--------------------|--------------|
| Packaging Method   | Kit, Package |
| Packaging Quantity | 100          |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR                                                  |



/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-357-D658  
IDC D-Sub: Plug Assembly, Signal, Cable to Cable, 2.16 mm

Also in the Series | CHAMP Docking Connectors

D-Sub Covers(27)

D-Sub Locking & Mounting(31)

Docking Connector Guide Hardware(5)

Docking Connectors(33)

IDC D-Sub Connectors(85)

PCB D-Sub Connectors(1)

Customers Also Bought





TE Part #1375820-6  
Receptacle Housing: 2.54mm, 1 Row, CST-100 II




TE Part #1-480425-0  
04P CMNL PLUG HSG P/M NATL



TE Part #170361-1  
UNIV M-N-L SOC. 26-22 AWG




TE Part #170360-1  
UNIV M-N-L PIN 22-18 AWG



TE Part #104505-3  
MTE PIN LP



TE Part #1-770010-0  
UMN II SOK SN/AUNI/PHBZ LF



TE Part #1-582843-3  
47 AMP BLADE HDR ASSY/MIL



TE Part #1-111623-0  
044 2MM CTR 30DP FT



TE Part #148423-5  
EURO TYPE M REC 42+6, THIN STK



TE Part #794272-1  
03P UMN WIRE SEAL

Documents

Product Drawings

COVER KIT 180 DEG 14 POS BLK

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2-552079-1\_G.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-552079-1\_G.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-552079-1\_G.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets





Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English