2057162-1 ✔ ACTIVE

TE Internal #: 2057162-1

SFP/SFP+/zSFP+, Cage, Data Rate (Max) 16 Gb/s, Elastomeric Gasket, SFP+, Port Matrix Configuration 1 x 4, Through Hole - Press-Fit, 4 Port

View on TE.com >

Connectors > Pluggable IO Connectors & Cages > SFP/SFP+/zSFP+



Pluggable I/O Product Type: **Cage**

Data Rate (Max): **16 Gb/s**

EMI Containment Feature Type: **Elastomeric Gasket**

Pluggable I/O Applications: **SFP+**

Included Lightpipe: **No**

Features

Product Type Features

Form Factor	SFP+
Cage Type	Ganged
Pluggable I/O Product Type	Cage
Connector System	Cable-to-Board
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Port Matrix Configuration	1 x 4
Number of Ports	4

Electrical Characteristics

Data Rate (Max)	16 Gb/s

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Press-Fit

Mechanical Attachment

PCB Mounting Style	Through Hole - Press-Fit
Connector Mounting Type	Board Mount

Housing Features

Cage Material	Nickel Silver

Dimensions

Tail Length	2.05 mm[.081 in]
PCB Thickness (Recommended)	1.5 mm[.059 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Heat Sink Compatible	No
For Use With Pluggable I/O Products	SFP+ SMT Connector
Pluggable I/O Applications	SFP+

Packaging Features

Packaging Method	Box & Tray, Box

Other

EMI Containment Feature Type	Elastomeric Gasket
Included Lightpipe	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-C11-H50626
SFP+ to SFP+ I/O Cable Assembly: 30 AWG



TE Part # CAT-C11-N490333
QSFP28-Four SFP+ Cable Assembly: 30 AWG



TE Part # CAT-C11-N490325
QSFP28-Four SFP+ Cable Assembly: 26 AWG



TE Part # CAT-C11-N49011142
SFP28 to SFP28 Cable Assembly: 32 AWG



TE Part # CAT-C11-N4901114
SFP28 to SFP28 Cable Assembly: 30 AWG



TE Part # CAT-C11-N49011
SFP28 to SFP28 Cable Assembly: 26 AWG



TE Part # CAT-Q17-N49011
QSFP56-Four SFP56 Cable Assembly: 30 AWG



TE Part # CAT-Q17-N490333
QSFP56-Four SFP56 Cable Assembly: 26 AWG



TE Part # CAT-C11-G28037
SFP56 to SFP56 Cable Assembly: 30 AWG



TE Part # CAT-C11-G28
SFP56 to SFP56 Cable Assembly: 26 AWG



TE Part # 4-2334985-2
SFP56 DIRECT ATTACH CA, 1M, 32AWG



TE Part # 2007099-1
SFP+ 1x4 Light Pipe Assembly



TE Part # 2170068-1
SFP+ 1x4 Light Pipe Assembly Low Profile



TE Part # CAT-C11-H5
SFP+ to SFP+ I/O Cable Assembly: 24 AWG



TE Part # CAT-C11-H506
SFP+ to SFP+ I/O Cable Assembly: 26 AWG



TE Part # CAT-C11-H5062
SFP+ to SFP+ I/O Cable Assembly: 28 AWG



TE Part # 2142970-1
CABLE ASSY, MICRO SFP+ TO STD SFP+, 0.5M



TE Part # 2142970-2
CABLE ASSY, MICRO SFP+ TO STD SFP+, 1M



TE Part # 2142970-3
CABLE ASSY, MICRO SFP+ TO STD SFP+, 2M



TE Part # 2142970-4
CABLE ASSY, MICRO SFP+ TO STD SFP+, 3M

Customers Also Bought



TE Part #1871058-2
PCI EXPRESS CONN. EON TYPE, 64P, L=2.0



TE Part #1-6450162-2
MBXL R/A RCPT 4P+12S




TE Part #1551892-2
Cage Assy Behind Bezel QSFP28



TE Part #6450814-1
MBXL VERT HDR STR 2ACP+12S



TE Part #1888542-3
MJ,10MM,8P,WAVE PANEL TABS,SN



TE Part #1-1775059-1
SD CONN RVS PUSH-PUSH 30u" Au



TE Part #1-2170704-3
CAGE ASSY, QSFP28 1X1, SPRING, CZ_HS



TE Part #1-5767096-0
MICT,REC,114,ASY,.025,TAPE,CAP



TE Part #1410477-2
MULTI-GIG GD PIN KEY/ESD NI PL

TE Part #1367627-1
light pipe assy, 1x1 sfp

Documents

Product Drawings

SFP+ 1X4 Cage Assembly, PF, EF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2057162-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2057162-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2057162-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications

Application Specification

English