



Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Conducting Accessories



Conducting Accessory Type: **Short Circuit Bridge**

Number of Poles: **3**

Primary Product Color: **Yellow**

Product Spacing: **8 mm [.315 in]**

Contact Current Rating (Max): **5 A**

Features

Product Type Features

Conducting Accessory Type	Short Circuit Bridge
---------------------------	----------------------

Configuration Features

Number of Poles	3
-----------------	---

Electrical Characteristics

Current Rating (IEC)	5 A
----------------------	-----

Body Features

Plastic & Resin Material Type	Polyamide
Product Weight	3.4 g[.119 oz]
Primary Product Color	Yellow

Contact Features

Contact Current Rating (Max)	5 A
------------------------------	-----

Dimensions

Tool Size	3.5 mm[.138 in]
Product Depth	13.9 mm[.547 in]
Product Width	8 mm[.315 in]
Product Height	24.6 mm[.968 in]
Product Spacing	8 mm[.315 in]



Usage Conditions

Storage Temperature Range	-55 – 110 °C[-67 – 230 °F]
Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Industry Standards

IP Rating	IP20
-----------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1SNK508011R0000
ZS10-R1




TE Part # 1SNK508151R0000
ZS10-PE-R1




TE Part # 1SNK508310R0000
ZS10-ST



TE Part # 1SNA115914R0700
D6/8.ST.RS



TE Part # 1SNK508311R0000
ZS10-ST-T4




TE Part # 1SNA115831R0400
D6/8.ST1.RS.IP20

Customers Also Bought



TE Part #1SNK805910R0000
EDK2.5-22



TE Part #1SNK806010R0000
ZDK4-22




TE Part #1SNA115685R1200
M6/8.RS




TE Part #1SNA116536R0500
PC6-3




TE Part #1SNA116720R2100
SCMA5D




TE Part #1SNA116728R2500
SCMA5



TE Part #1SNA234055R2400
RC810 141->150 (X10) VERTICAL



TE Part #1SNA234056R2500
RC810 151->160 (X10) VERTICAL



TE Part #1SNA234057R2600
RC810 161->170 (X10) VERTICAL



TE Part #2150283-1
OCEAN_2.0_Applicator-S-080F130F

Documents



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1SNK900653R0000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1SNK900653R0000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNK900653R0000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SC-JB8-3

English

SNK SERIES TERMINAL BLOCKS

English

ENTRELEC Terminal Block - Master Catalog

English

ENTRELEC Terminal Blocks Catalogue (RUS)