

1SNA173220R0500 ✓ ACTIVE


TE Internal #: 1SNA173220R0500

Terminal Block & Strip Mounting & Retention Accessories, Module Block/Mounting Rail Assembly, Product Length .295 in [7.5 mm], DIN Rail

[View on TE.com >](#)



Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Mounting & Retention Accessories



Mounting & Retention Accessory Type: **Module Block/Mounting Rail Assembly**

Product Length: **7.5 mm [.295 in]**

Connector Mounting Type: **DIN Rail**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Body Features

Mounting & Retention Accessory Type	Module Block/Mounting Rail Assembly
-------------------------------------	-------------------------------------

Mechanical Attachment

Connector Mounting Type	DIN Rail
-------------------------	----------

Dimensions

Product Length	7.5 mm [.295 in]
----------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1SNK505010R0000
ZS4



TE Part # 1SNK505020R0000
ZS4-BL



TE Part # 1SNK505030R0000
ZS4-OR



TE Part # 1SNK505060R0000
ZS4-YL



TE Part # 1SNK505061R0000
ZS4-GN



TE Part # 1SNK505062R0000
ZS4-RD



TE Part # 1SNK505063R0000
ZS4-PR



TE Part # 1SNK505064R0000
ZS4-BR



TE Part # 1SNK505065R0000
ZS4-WH



TE Part # 1SNK505066R0000
ZS4-BK





TE Part # 1SNK505150R0000
ZS4-PE



TE Part # 1SNK505210R0000
ZS4-D2



Customers Also Bought



Documents



Product Drawings

[PR30](#)

English

Datasheets & Catalog Pages

[PR30](#)

English

[SNK SERIES TERMINAL BLOCKS](#)

English

[ENTRELEC Terminal Block - Master Catalog](#)

English