




Connectors > Pluggable IO Connectors & Cages > SFP/SFP+/zSFP+



Pluggable I/O Product Type: **Accessory**

Included Lightpipe: **Yes**

Integrated Lightpipes: **Yes**

Lightpipe Configuration: **Dual Square**

Lightpipe Style: **Standard**

Features

Product Type Features

Form Factor	SFP
Pluggable I/O Accessory Type	Lightpipe
Pluggable I/O Product Type	Accessory
Integrated Lightpipes	Yes
Sealable	No

Configuration Features

Lightpipe Configuration	Dual Square
Lightpipe Style	Standard
Lightpipe Profile	Standard

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Other

Included Lightpipe	Yes
--------------------	-----

Product Compliance



For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1761394-1

DUST COVER, SFP, GANGED & STACKED

Customers Also Bought



 TE Part #100616-1 8/8 MOD.JACK ASSY TE SHIELDED	 TE Part #1437654-1 6PCV-17-1206=6PCV ASSEMBLY	 TE Part #1-87993-6 16 MODI BDMNT RCPT SR .156CL	 TE Part #1-1879500-4 CRGH2010 5% 47K 1W
 TE Part #1-770969-0 06P MINI UMNL R/A HDR ASSY SN	 TE Part #1-770178-1 06P MINI UMNL ASSY VO SNAU LF	 TE Part #1-770170-1 03P MINI UMNL ASSY VO SNAU LF	 TE Part #1-770174-1 04P MINI UMNL ASSY VO SNAU LF
 TE Part #T1937031000-009 H3APR-MAGSW-EMC-C	 TE Part #1-1969543-2 ASSY, HDR, VERT, BOSSED, DUAL ROW, EP2.5		

Documents

Product Drawings
SFP 1X2 LIGHT PIPE ASSY

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_1761011-3_A.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_1761011-3_A.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1761011-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance



TE Material Declaration

English