



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: **Ferrule**

Ferrule Type: **Split-Ring**

Compatible With Connector Shell Size: **5**

Shielded: **Yes**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Ferrule

Body Features

Ferrule Material	Aluminum
Ferrule Diameter	20.07 mm[.79 in]
Ferrule Type	Split-Ring

Dimensions

	.71 – .75 in
--	--------------

Operation/Application

Compatible With Connector Shell Size	5
Shielded	Yes

Packaging Features

Packaging Quantity	1
Packaging Method	Package



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5745175-1
CABLE CLAMP KIT, SZ 5



TE Part # 5747098-1
CABLE CLAMP KIT, SZ 5

Also in the Series | **AMPLIMITE Kit**



D-Sub Backshells & Clamps(136)

D-Sub Contact Accessories(1)

D-Sub Covers(3)

D-Sub Locking & Mounting(122)

Customers Also Bought

TE Part #0462-209-16141
DEUTSCH SOLID CONTACTS

TE Part #1-1986693-0
STR PLUG SPRING TYPE LH 10P, 3.50 mm

TE Part #1-745508-0
FERRULE SPLIT RING, HD

TE Part #1-786863-7
IDC D-Sub: Receptacle Kit, Panel Mount, Signal, 1.27 mm

TE Part #YDTS20W11-35ANV001
D38999: Square Flange, 11-35 insert

TE Part #1-480698-0
02P UMNL PLUG HSG NATL

TE Part #1-51692-6
N SERIES PLUG RG 217

Documents

Product Drawings
FERRULE SPLIT RING, HD

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-745508-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-745508-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-745508-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English