



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.5% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1-2308272-5
CABLE CLAMP FOR SIZE 4-5STD/5QL
SHELL

TE Part #1623440-1
CRG1206 1% 1K0

TE Part #1-2176316-1
MELF SMA_A 680R 0.1% 15PPM 0207
1W

TE Part #1-829261-6
HD FEMALE SCREWLOCK

TE Part #1623413-1
CRG1206 1% 120R

TE Part #9-1879223-0
CPF 0603 2K37 0.1% 25PPM 1K RL

TE Part #1-1879666-5
H8 187K 0.1% 15PPM

TE Part #1-2308298-1
DOUBLE SIDED QLPIN BULKHEAD

TE Part #1-925370-3
MOD IV REC HSG, 2X13P

TE Part #1-2176316-0
MELF SMA_A 560R 0.1% 15PPM 0207
1W

Documents

Product Drawings
HD FEMALE SCREWLOCK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-829261-4_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-829261-4_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-829261-4_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.