



All 0.3mm FPC Connectors (6)

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                         |
|-----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                               |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                               |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                                 |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2019 (197)<br>SVHC > Threshold:<br>Not Yet Reviewed |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                                     |
| Solder Process Capability                     | Reflow solder capable to 245°C                                                                                                          |


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought



TE Part #2-1734592-3  
0.5mm FPC Connectors



TE Part #282845-3  
TERM-BLOK,PCB MNT,90DG,3P,7.62



TE Part #282834-7  
TERMI-BLOK PCB MOUNT, 90 7P.



TE Part #2118708-2  
1 PC STD SHIELD, CRS-26.21X26.21X5.08MM



TE Part #3-2176325-1  
CRGP 0402 3K3 1%



TE Part #2-2176371-5  
RQ 0603 8K25 0.1% 10PPM 5K RL



TE Part #826634-8  
08P MODU 2 PIN HDR



TE Part #2311763-2  
D-Sub Receptacle Assembly: Right Angle, 2.29mm



TE Part #1-84984-2  
1mm FFC DIP V ASSY 12P TUBE

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-2013496-6\_D\_c-1-2013496-6-d.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-2013496-6\_D\_c-1-2013496-6-d.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-2013496-6\_D\_c-1-2013496-6-d.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773959-6-flexible-printed-circuit-con

English

8-1773459-2\_Fine\_Pitch\_FPC\_conn\_QRG

English



1-1773959-7-FPC-Connectors-CN

Product Specifications

0.3FPC NARROW Spec.

Japanese

Product Specification

Japanese

Instruction Sheets

0.3FPC Narrow BF-L

Japanese

Instruction Sheet (non U.S.)

Japanese