



Terminals & Splices > Splices



Splice Product Type: **Splice**
Terminal & Splice Type: **Splice**
Wire Size: **.129 – .326 mm²**
Sealable: **No**

Features

Product Type Features

Discrete Wire Type	Stranded
Barrel Style	Standard
Splice Product Type	Splice
Sealable	No
Splice Type	Butt Splice
Serrated	No
Splice Accessory Type	Splice
Splice Barrel Type	Closed Barrel
Splice Wire/Cable Type	Copper
Insulated	Yes
Support Style	Insulation Support

Electrical Characteristics

Operating Voltage	600 V
-------------------	-------

Body Features

Insulation Sleeve Material	Nylon
Insulation Type	Pre-Insulated
Weight per Piece	.411 g
Plating Material	Tin
Splice Features	Standard
Splice Material	Copper



Splice Color	Yellow
--------------	--------

Contact Features

Class	1 & 2
Terminal & Splice Type	Splice

Termination Features

Termination Method	Crimp
--------------------	-------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	202 – 810 CMA
Splice Wire Insulation Diameter (Max)	2.08 mm[.082 in]
Barrel Inside Diameter	2.13 mm[.084 in]
Splice Overall Length	22.61 mm[.89 in]

Usage Conditions

Insulation Requirement	Fully Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified Splice	Yes
-----------------------------	-----

Packaging Features

Packaging Quantity	100
Splice Packaging Method	Loose Piece

Other

Comment	Marking: Commercial 26-22- Military 26-24 in accordance with MIL-T-7928., Small packaging of 323994.
Military Category	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 46121
DAHT PG PIDG 26-22 ASSY



TE Part # 59275
T-HEAD PIDG PG SH 26-20 ASSY




TE Part # 189721-1
HAND NON-LOGIC POWER UNIT



TE Part # 189722-1
FOOT NON-LOGIC POWER UNIT



TE Part # 1901260-1
CCII 16MAX ASSY



TE Part # 1490567-1
HAND NON-LOGIC SHORT POWER UNI

Also in the Series | PIDG



Compression Connectors(17)



Crimp Terminal Housings(1)



Crimp Wire Pins, Tabs & Ferrules(41)



Knife Disconnects(11)



PCB Terminals(9)



Portable Crimp Tools(2)



Quick Disconnects(53)



Ring Terminals & Spade Terminals(862)



Special Purpose Terminals(1)




Splices(48)


Customers Also Bought



TE Part #1761685-9
IDC LOW PRO HDR 26P VERT SHT LAT




TE Part #1SNK140000R0000
MC512



TE Part #216520-4
30P.IEC-F FEM.CONN.



TE Part #392758-000
STD SNAP-ON MARKERS



TE Part #1658543-3
D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20



TE Part #7-1393788-5
AXICOM P2 STANDARD



TE Part #3-641438-2
02P MTA156 PSTD CONN ASSY WHT



TE Part #4-641190-4
Nylon Gold Plated Receptacle: 2.54 mm, No Mating Alignment, MTA 100



Documents

Product Drawings

SMP 0-0323994-0

English

Datasheets & Catalog Pages

RADIATION_RESISTANT_PRE-INSULATED_TERMINALS_SPLICES

English

Product Specifications

Application Specification

English