111547-2 ✔ ACTIVE

AMP-LATCH

TE Internal #: 111547-2

TE Internal Description: 014 UNIV I/O STRAIN RELIEF

Pin Connector: Strain Relief, Universal

View on TE.com >

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Connector Accessories >

Pin Connector: Strain Relief, Universal







Flat Flexible Cable Accessory Type: **Strain Relief**

All Pin Connector: Strain Relief, Universal (12)

Features

Product Type Features

Flat Flexible Cable Accessory Type	Strain Relief

Body Features

Primary Product Material	Glass-Filled Polyester
Primary Product Color	Black

Dimensions

	1.14 in

Industry Standards

CSA File Number	LR 7189
Agency/Standard	CSA, UL
UL Rating	Recognized
UL File Number	E28476

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Other

Comment	Receptacle Connector

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts



TE Part # 1-111446-5
14 UNIV I/O, NO EARS,LEAD FREE



TE Part # 1-111492-6
014 UNIV I/O 30DP NO EARS LTCH




TE Part # 1-111504-5
014 UNIV I/O 30DP NO EARS LTCH

Customers Also Bought




TE Part #111547-8
Pin Connector: Strain Relief, Universal




TE Part #1-111446-5
14 UNIV I/O, NO EARS,LEAD FREE



TE Part #1-87499-3
08 MODIV HSG SR MRKD .100CL



TE Part #102541-8
20 AMPMODU MT COVER DR .100CL




TE Part #102541-5
14 AMPMODU MT COVER DR .100CL



TE Part #1241148-5
0-966711-5MAGAZ320X



TE Part #1490019-8
CRIMPER, WIRE



TE Part #1333230-3
ANVIL, COMB.



TE Part #NB19234001
RNF-100-1/8-CL-SP

Documents

Product Drawings

014 UNIV I/O STRAIN RELIEF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_111547-2_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_111547-2_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_111547-2_N.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Ribbon Cable Interconnect Solutions

English

Product Specifications

Application Specification

English