104891-8 ✔ ACTIVE

AMPMODU | AMPMODU 50/50 Grid

TE Internal #: 104891-8

AMPMODU 50/50 Grid, PCB Connector Covers, Cover, 80 Position, 1.27mm [.05in] Centerline, 2 Row, Polyester, Row-to-Row Spacing . 05 in [1.27 mm]

View on TE.com >

Connectors > PCB Connectors > PCB Connector Accessories > Protection & Strain Relief > PCB Connector Covers



Protection & Strain Relief Accessory Type: **Cover**

Number of Positions: **80**

Centerline (Pitch): **1.27 mm [.05 in]**

Number of Rows: **2**

Primary Product Material: **Polyester**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover
Product Profile	Standard
Connector Cover Type	Terminating
Sealable	No

Configuration Features

Number of Positions	80
Number of Rows	2

Body Features

Connector Cover Side	Front
Primary Product Color	Black
Primary Product Material	Polyester

Contact Features

Contact Current Rating (Max)	5 A

Housing Features

Centerline (Pitch)	1.27 mm[.05 in]

Dimensions

Row-to-Row Spacing	1.27 mm[.05 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]

Operation/Application

Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 104652-8
80 50/50 GRID DRST SFMNT RCPT


Also in the Series | AMPMODU 50/50 Grid



Board-to-Board Headers & Receptacles(290)




Insertion & Extraction Tools(1)



PCB Connector Covers(9)



Ribbon Cable Connectors(34)



Wire-to-Board Headers & Receptacles (12)

Customers Also Bought



TE Part #1658613-2
IDC D-Sub: Plug Assembly, Low Profile, Signal, 2.77 mm



TE Part #1658612-2
IDC D-Sub: Receptacle Assembly, Low Profile, Signal, 2.77 mm



TE Part #2-329940-1
TWIN THD RECEPT KIT



TE Part #104892-8
80 50/50 GRID CBLE RECP W/LTCH



TE Part #1-1478988-0
SMA B/HD JK DS RG405 GSS



TE Part #104895-8
80 50/50 GRID RA HDR W/LTCH



TE Part #1051032-1
SMA BULKHEAD JACK 2004 8207 92



TE Part #1-2204749-8
ELCON MICRO,RECEPTACLE, CONTACT, TIN



TE Part #2-1617076-4
3SBH1227A2 = M39016/53-008M

TE Part #ZPF000000000134122
D38999/33W11N

Documents

Product Drawings

80 50/50 GRID CABLE RCPT COVER

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_104891-8_C.3d_igs.zip

English

Customer View Model

ENG_CVM_104891-8_C.3d_stp.zip

English

Customer View Model

ENG_CVM_104891-8_C.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION1AND2

English

Fine Pitch Stacking Connectors - 1.27mm AMPMODU 50/50 Grid Connectors

English

Ribbon Cable Interconnect Solutions

English

Product Specifications

Application Specification

English