




SFP28

TE Internal #: 1658862-1
SFP/SFP+/zSFP+, Accessory, Data Rate (Max) 4 Gb/s, Included
Lightpipe, Port Matrix Configuration 2 x 1, All Four, Standard,
Standard, 1 Port

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > SFP/SFP+/zSFP+ > SFP+ Stacked Cage Assemblies



Pluggable I/O Product Type: **Accessory**
Data Rate (Max): **4 Gb/s**
Included Lightpipe: **Yes**
Port Matrix Configuration: **2 x 1**
Integrated Lightpipes: **No**

[All SFP+ Stacked Cage Assemblies \(122\)](#)

Features

Product Type Features

Form Factor	SFP
Pluggable I/O Accessory Type	Lightpipe Kit
Cage Type	Stacked
Pluggable I/O Product Type	Accessory
Integrated Lightpipes	No
Sealable	No

Configuration Features

Port Matrix Configuration	2 x 1
Lightpipe Configuration	All Four
Lightpipe Style	Standard
Lightpipe Profile	Standard
Number of Ports	1



Electrical Characteristics

Data Rate (Max)	4 Gb/s
-----------------	--------

Operation/Application

For Use With Pluggable I/O Products	Stacked SFP Cage Assembly
-------------------------------------	---------------------------

Packaging Features

Packaging Method	Tray
------------------	------

Other

Included Lightpipe	Yes
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # CAT-SF59-C117ST123
SFP+ Stacked Cage Assemblies



TE Part # 1367147-1
SFP COVER, UNPLATED



TE Part # 1367147-3
SFP COVER, UNPL, NO LOGO


Customers Also Bought



TE Part #2273101-4
M12 A-CODE FEMALE R/A PIGTAIL



TE Part #1558662-9
PCB Power Relay: 30 amp, Monostable DC




TE Part #3-647117-6
Nylon Right Angle PCB Header: 2.54 mm, Wire-to-Board, Through Hole, MTA 100



TE Part #1-530743-4
MINI BOX PIN HDR ASY 40 POS



TE Part #1600236-4
PAN MT PLUG, MBXL, 1P+24S+1P




TE Part #533286-9
HDI PIN ASSY 4 ROW 240 POS R/A




TE Part #1-2373378-2
12P,2MM,SHRD HDR,DRVT,SMD,0.76 AU,TB



TE Part #ZPF000000000033191
983-0S 12-03 P8



TE Part #1-2364573-6
AVH19 FLT SS LK R+P GRN 24V26A



TE Part #2176368-3
RQ 0603 52K3 0.1% 10PPM 1K RL

Documents

Product Drawings
SFP 2X1 LIGHT PIPE ASSY
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1658862-1_B.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1658862-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1658862-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English