1-643075-4 ✔ ACTIVE

MTA | MTA 100

TE Internal #: 1-643075-4


MTA 100, PCB Connector Covers, Strain Relief Covers, 14 Position, 2.54mm [.1in] Centerline, Nylon, Standard Product Profile

View on TE.com >

Connectors > PCB Connectors > PCB Connector Accessories > Protection & Strain Relief > PCB Connector Covers > Nylon PCB Connector Covers: 2.54mm, MTA 100







Protection & Strain Relief Accessory Type: **Strain Relief Covers**

Number of Positions: **14**

Centerline (Pitch): **2.54 mm [.1 in]**

Primary Product Material: **Nylon**

Product Profile: **Standard**

All Nylon PCB Connector Covers: 2.54mm, MTA 100 (54)

Features

Product Type Features

Protection & Strain Relief Accessory Type	Strain Relief Covers
Product Profile	Standard

Configuration Features

Number of Positions	14

Body Features

Primary Product Color	White
Primary Product Material	Nylon

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]

Usage Conditions

Compatible With IDC Installation Type Connector	Closed End
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]

Industry Standards

UL Flammability Rating	UL 94V-2

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts




TE Part # CAT-104MTA-NTPNR
Nylon Tin Plated Receptacle: 2.54mm, No Mating Alignment, MTA 100



TE Part # CAT-104MTA-NYLCC
Nylon PCB Connector Covers: 2.54 mm, MTA 100




TE Part # CAT-104MTA-PVUNH
Polyester Vertical PCB Header: 2.54 mm, Unshrouded, No Mating Alignment



TE Part # CAT-104MTA-NTPMR
Nylon Tin Plated Receptacle: 2.54mm, With Mating Alignment, MTA 100




TE Part # CAT-104CST-RCPHS
Receptacle Housing: 2.54mm, 1 Row, CST-100 II



TE Part # CAT-104MTA-PVUMH
Polyester Vertical PCB Header: 2.54 mm, With Mating Alignment, Unshrouded




TE Part # CAT-104MTA-PRUMH
Polyester Right Angle PCB Header: 2.54mm, Wire-to-Board, MTA 100



TE Part # CAT-104MTA-PRUSH
Polyester Right Angle PCB Header: 2.54mm, Unshrouded, MTA 100



TE Part # CAT-104MTA-PVSHH
Polyester Vertical PCB Header: 2.54 mm, Shrouded, MTA 100




TE Part # CAT-104MTA-PVBRH
Polyester Vertical PCB Header: 2.54 mm, Breakaway, MTA 100




TE Part # CAT-104MTA-PRBRH
Polyester Right Angle PCB Header: 2.54mm, Breakaway, MTA 100



TE Part # CAT-104MTA-NGPNR
Nylon Gold Plated Receptacle: 2.54 mm, No Mating Alignment, MTA 100




TE Part # CAT-104MTA-NGPMR
Nylon Gold Plated Receptacle: 2.54 mm, With Mating Alignment, MTA 100



TE Part # CAT-104MTA-NTPMP
Nylon Tin Plated Plug: 2.54mm, With Mating Alignment, MTA 100




TE Part # CAT-104MTA-PRSMH
Polyester Right Angle PCB Header: 2.54mm, Shrouded, With Mating Alignment



TE Part # CAT-104MTA-NGPMP
Nylon Gold Plated Plug: 2.54mm, With Mating Alignment, MTA 100




TE Part # 4-644892-4
14P CST100 SHRD HDR ASSY LF



TE Part # 4-644893-4
14P CST100 SHRD HDR ASSY LF



TE Part # 4-644894-4
14P CST100 SHRD HDR ASSY LF




TE Part # 4-644896-4
14P CST100 SHRD HDR ASSY LF

Also in the Series | MTA 100




Insertion & Extraction Tools(2)



PCB Connector Covers(107)



PCB Connector Keying(1)



Standard Rectangular Connectors (1730)



Wire-to-Board Connector Contacts(18)




Wire-to-Board Headers & Receptacles (1182)

Customers Also Bought



TE Part #1-643075-0

Nylon PCB Connector Covers: 2.54 mm, MTA 100




TE Part #745183-2

D-Sub Receptacle Assembly: Vertical, Shell Size 1, 2.74mm



TE Part #1-480284-0

08P CMNL CAP HSG M/M NATL



TE Part #1-643067-0

10P MTA156 MOLDED COVER



TE Part #1-640457-2

Polyester Right Angle PCB Header: 2.54mm, Unshrouded, MTA 100



TE Part #1-6609035-3

CORCOM SK SERIES SINGLE PHASE FILTERS



TE Part #207893-1

CONTACT PIN ASSY.



TE Part #1878643-8

M5031W

Documents

Product Drawings

14P MTA100 MOLDED COVER

English

CAD Files

3D PDF

3D

3D PDF

English

Customer View Model

ENG_CVM_1-643075-4_G.3d_igs.zip

English

Customer View Model

ENG_CVM_1-643075-4_G.3d_stp.zip

English

Customer View Model

ENG_CVM_1-643075-4_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-643075-4_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-643075-4_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-643075-4_N.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

MTA, CST-100 II, SL-156 and AMP Economy Power (EP) Connectors

English

Product Environmental Compliance

MD_1-643075-4_09192017015_dmtec

English

MD_1-643075-4_09192017015_dmtec

English

Instruction Sheets

Instruction Sheet (U.S.)

English