




Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



SolderSleeve Shield Terminator Operating Temperature (Max): 150 °C

SolderSleeve Shield Terminator Expanded Inside Diameter (Min): 5.08 mm [.2 in]

SolderSleeve Shield Terminator Recovered Inside Diameter (Max): 2.16 mm [.085 in]

Pre-Installed Lead: Yes

Wire Temperature (Max): 125 °C

Features

Configuration Features

Pre-Installed Lead	Yes
--------------------	-----

Dimensions

SolderSleeve Shield Terminator Expanded Inside Diameter (Min)	5.08 mm[.2 in]
SolderSleeve Shield Terminator Recovered Inside Diameter (Max)	2.16 mm[.085 in]

Usage Conditions

SolderSleeve Shield Terminator Operating Temperature (Max)	150 °C
Wire Temperature (Max)	125 °C

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (37% in Solder) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.



Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CJ2087-000
HL2010E-KIT-120V

Customers Also Bought

TE Part #320564
PIDG RING TONGUE TERMINALS

TE Part #225532-3
SMA PLUG FLEX

TE Part #323171
TERMINAL,SOLIS R HR 6 5/16

TE Part #1958285-1
SOLISTRAND 6 S-T HR RING 1/4

TE Part #217675-000
55PC0811-22-5LL-CS2502

TE Part #169161-000
55PC1121-20-2/6-9CS2502

TE Part #323067
DIAMOND GRIP 12-10 HR R 8

TE Part #274307-000
D-436-0184



Documents

Product Drawings

S03-08-R-100HN

English

Datasheets & Catalog Pages

Raychem Electrical Interconnect Products

English

Product Specifications

Product Specification

English