
1393560-5 ✔ ACTIVE

TE Internal #: 1393560-5

Ribbon Cable Connectors, Signal

View on TE.com >

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors




Circuit Application: **Signal**

Features

Operation/Application

Circuit Application	Signal

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.35% in Component Part) **Article Safe Usage Statements:** Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these

limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Customers Also Bought



TE Part #1-1393239-6
RT114110



TE Part #102169-1
MOD V NO STRIP PLTD SN




TE Part #1-1879022-3
SMD Power Resistor: 7 Watt, 200-2M Ohm



TE Part #1337810-1
50 OHM COAX SMA STR PLUG ELB P



TE Part #1337808-3
50 OHM COAX SMA STR PLUG STR P



TE Part #1487588-1
USB, A-B, 28/24, WHITE, 2.0M



TE Part #1-1625958-2
HB01RE 1G0 1% 100PPM



TE Part #1-1337624-0
N Str Adp JJ 50Ohm Nickel Pltd



TE Part #1-1478046-0
BNC BH Adp JJ 50Ohm Silver Plt

TE Part #T4171010005-002
M12,REAR MOUNTING,MALE,A,5P,0.5 M WIRE

Documents

Product Drawings

C42334A 383C911=SUB D BOLZEN A

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1393560-5_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1393560-5_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1393560-5_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.