1-2308349-2 ✔ ACTIVE

Rail D-Sub Backshells

TE Internal #: 1-2308349-2

Rail D-Sub Backshells, D-Sub Backshells & Clamps, Crimp Flange, Shielded, Wire & Cable, Operating Temperature Range -40 – 90 °C [-40 – 194 °F]

View on TE.com >

Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps > CRIMP FLANGE FOR SIZE 1-3STD/1-4QL SHELL






D-Shaped Connector Accessories: **Crimp Flange**

Shielded: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Operating Temperature Range: **-40 – 90 °C [-40 – 194 °F]**

All CRIMP FLANGE FOR SIZE 1-3STD/1-4QL SHELL (14)

Features

Product Type Features

Clam Shell Length	Standard
Grommets	Without
Slide Latch	Without
Product Type	Backshell/Cable Clamp
D-Shaped Connector Accessories	Crimp Flange
Connector & Contact Terminates To	Wire & Cable

Mechanical Attachment

Screw & Hole Thread Size	None

Usage Conditions

Operating Temperature Range	-40 – 90 °C[-40 – 194 °F]

Operation/Application

Shielded	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant

EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.5% in Component Part) **Article Safe Usage Statements:** Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-R131-B2745
CRIMP BARREL


Also in the Series | Rail D-Sub Backshells



Crimp D-Sub Connectors(10)



D-Sub Backshells & Clamps(143)




D-Sub Connector Contacts(5)

Customers Also Bought



TE Part #2-2308348-2
CRIMP FLANGE FOR SIZE 4-5STD /5QL SHELL




TE Part #4-1879463-8
Thick Film Resistor: Current Sense



TE Part #2-2317658-6
AV25 DPL 3A MOVING RING POWER WHITE 24V



TE Part #5-103960-9
2X10 MTE RCPT SR LATCH .100CL



TE Part #697175-000
TXR40AB90-1210AI



TE Part #YDTS24Z19-32SNV001
Jam Nut: D38999, 19-32 Insert, Black Zinc Nickel Plating



TE Part #546410-000
TTP CONTINUOUS POLYESTER LABEL DECALS



TE Part #1SNK169002R0000
MC812PA L1-L2-L3-N-PE (x20) Vertical



TE Part #5-103944-9
2X10 MTE SHRD PIN SR POL .100

Documents

Product Drawings

CRIMP FLANGE 2 SMALL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2308349-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2308349-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2308349-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

Rail D-Sub Backshells Flyer

English