



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



SolderSleeve Shield Terminator Product Type: **Shield Terminator**

SolderSleeve Shield Terminator Operating Temperature (Max): **125 °C**

SolderSleeve Shield Terminator Expanded Inside Diameter (Min): **13 mm [.512 in]**

SolderSleeve Shield Terminator Recovered Inside Diameter (Max): **7.01 mm [.276 in]**

Pre-Installed Lead: **Yes**

Features

Product Type Features

Temperature Indicator	No
SolderSleeve Shield Terminator Product Type	Shield Terminator

Configuration Features

Pre-Installed Lead Type	XL Polyethylene
Pre-Installed Lead	Yes

Body Features

Lead Color	Green
Lead Plating Material	Tin
Lead Stranding	Stranded

Dimensions

Pre-Installed Lead Wire Size	.38 mm ²
Overall Length	45.5 mm[1.79 in]
Shield Outside Diameter (Min)	8.9 mm[.35 in]
Jacket Outside Diameter	13 mm[.51 in]
SolderSleeve Shield Terminator Expanded Inside Diameter (Min)	13 mm[.512 in]
SolderSleeve Shield Terminator Recovered Inside Diameter (Max)	7.01 mm[.276 in]

Usage Conditions

SolderSleeve Shield Terminator Operating Temperature (Max)	125 °C
--	--------



Resistance Properties	Splash Protection
Wire Temperature (Max)	85 °C

Industry Standards

MIL/NAS Specification (MIL-S-83519, NAS-1747)	No
Government Qualified	No

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (32% in Solder) Cd (18% in Solder) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V

Also in the Series | Raychem CWT



SolderSleeve Shield Terminators(27)



Splices(1)


Customers Also Bought



TE Part #0660-206-0882
CONT PIN



TE Part #0660-206-1282
CONT PIN



TE Part #265042-002
81044/9-16-9



TE Part #2-2319847-3
END STACK DIP 2P G RAISED T&R




TE Part #1-88997-3
2.54mm FFC Connectors Pin Contacts




TE Part #DTS26W19-35SN
D38999: Straight Plug, 19-35 Insert




TE Part #109858-000
D-181-1222-90/9



TE Part #149657-000
B-020-20-N



TE Part #282225-001
81044/12-16-5



TE Part #2-1393310-0
26A1348C=TERMINAL,CRMP,OC.250,



Documents

Product Drawings

CWT-13-W122-5

English

Datasheets & Catalog Pages

1654025_Sec8_B-155_CWT_D-110_D-1744

English

Raychem Electrical Interconnect Products

English

Product Specifications

Product Specification

English

SolderSleeve One-Step Wire and Cable Terminators Installation Procedures for CWT and B-155 Products

English