




Connectors > Terminal Blocks & Strips > Barrier Strips



Number of Positions: 5
Centerline (Pitch): 11.1 mm [.438 in]
Number of Rows: 1
Circuit Application: Power

Features

Product Type Features

Product Type	Barrier Strip
--------------	---------------

Configuration Features

Number of Positions	5
Number of Rows	1

Housing Features

Centerline (Pitch)	11.1 mm[.438 in]
--------------------	------------------

Dimensions

Length	76.2 mm[3 in]
--------	---------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Package
Packaging Quantity	50

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2021
(211)
Candidate List Declared Against: JUL 2019
(201)
SVHC > Threshold:
Not Yet Reviewed


Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Wave solder capable to 265°C
---------------------------	------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1546977-5
SSB7TG050501=TERM BLOCK ASSY



TE Part # 1776858-5
SSB7TP050101=TERM BLOCK ASSY



TE Part # 1-1437416-7
SSB7FP050202=SSB STRIP 7/16 5



TE Part # 1-1437416-9
SSB7FP050402=SSB7FP ASSY

Customers Also Bought



TE Part #2-2176050-9
Thick Film Resistor: Current Sense



TE Part #172338-1
MINI UMNL PLUG HOUSING 4P



TE Part #172336-1
2P MINI UMNL PLUG HOUSING



TE Part #170362-3
MINI UNIVERSAL M-N-L SOCKET



TE Part #2-282836-6
TERMI-BLOK PCB MOUNT 90 25P.

TE Part #201145-2
COAX MINIATURE SOCKET ASSY

TE Part #202648-4
PIN MODULE, 11 POSN, G-SERIES

TE Part #YDTS24F17-06BNV001
D38999: Jam Nut, 17-06 Insert, Electroless Nickel Plating

TE Part #1579024-8
HTV10 HAND TOOL MATE-N-LOK, 0.2-0.82

TE Part #1-480698-0
02P UMNL PLUG HSG NATL

Documents

Product Drawings

7C1N05=SSB 7/16 SAFE CVR 5 CKT

English

Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS

English