




Connectors > Automotive Connectors > Connector Accessories > Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Cover - Cable Exit**
Cable Exit Angle: **90° (Right Angle)**
Strain Relief: **With**
Primary Product Color: **Yellow**
Primary Product Material: **PBT**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover - Cable Exit
Connector System	Wire-to-Board, Wire-to-Device

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Cable Exit Angle	90° (Right Angle)
Primary Product Color	Yellow
Primary Product Material	PBT

Mechanical Attachment

Strain Relief	With
---------------	------

Dimensions

Cable Bundle Diameter	5.7 mm[.224 in]
-----------------------	-----------------

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Industry Standards



UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Bag
------------------	-----

Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 353746-1
SQUIB AIRBAG /FERRITE

TE Part # 353744-7
SQUIB AIRBAG/HSG-MAIN

TE Part # 353744-2
FIX-IN SQUIB CONN HSG-MAIN BK

Customers Also Bought

TE Part #170326-1
187 PL MKII REC. 18-14AWG PTBR

TE Part #170325-1
187 PL MKII REC. 20-16AWG PTBR

TE Part #170328-1
250 PL MKII REC. 18-14AWG PTBR

TE Part #1-1376357-1
SIGNAL HEADER

TE Part #1376113-5
HIGH PIN COUNT HEADER

TE Part #1473369-7
SQUIB 11DIA SCR ASSY CODE-A GR

TE Part #1473369-9
SQUIB 11DIA SCR ASSY 8.8MM TYPE

TE Part #170030-5
FF 250 TAB 20-14AWG PTBR

TE Part #172383-5
FF 250 REC HSG 2P NYLON BLUE P/M

TE Part #CP4914-000
ES2000-NO.2-B9-0-60MM-SH

Documents

Product Drawings
SQUIB AIRBAG/HSG-LID

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_353745-7_A1.3d_igs.zip



English

Customer View Model

[ENG_CVM_353745-7_A1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_353745-7_A1.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

Japanese

Product Specification

Japanese

Product Environmental Compliance

TE Material Declaration

English

Instruction Sheets

Instruction Sheet (non U.S.)

English